


NOTES:

1. MATERIAL: ASTM A536 GR 65-45-12 DUCTILE IRON.
2. THIS GRATE HAS 40 IN² (39%) OPEN AREA.
3. THIS GRATE IS RATED FOR LOAD CLASS "D" PER DIN/EN 1433 SECTION 9.1.3. WHEN USED WITH A FRAME IT IS RATED FOR CLASS "E".

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC	
CHK	<i>WRJ</i>	3/27/90	14#		S	
ENG	<i>M&F</i>	3/27/90	SCALE		REV	
APR	<i>MSP</i>	3/27/90	3"=1'		D	
APR	<i>F.M.S</i>	3/27/90	SIZE		10/11	
ESR OR PROJECT NUMBER			DRAWING DESCRIPTION		DRAWING NUMBER	
90151			POLYCAST [®] DUCTILE IRON GRATE		DG0641D	
SHEET 1 OF 1						