



4				3			2			1			
CATALOG NO	APPLICATION RANGE	STRAND SIZE & CONSTRUCTION	NO. OF WIRES	COLOR CODE	DIM "A"	DIM "B"	DIM "C"	RBS (POUNDS)	SECOND COLOR MARK	STANDARD PACK QUANTITY	ITEM	DESCRIPTION	MATERIAL
FWDE 1102	0.174 - 0.203 [4.42 - 5.15]	3/16 (7W)	4	RED	20 [508]	15.25 [387]	0.938 [23.83]	3990 [17.7]	PRESENT	100	1	FORMED WIRE DEADENDS	GALVANIZED STEEL
FWDE 1103	0.204 - 0.230 [5.18 - 5.84]	7/32 (7W)	4	GREEN	24 [610]	18.6 [610]	0.938 [23.83]	5400 [24.0]	PRESENT	50			
FWDE 1104	0.231 - 0.259 [5.86 - 6.57]	1/4 (3W or 7W)	5	YELLOW	25 [635]	20.6 [524]	1.000 [25.40]	6650 [29.6]	PRESENT	50			
FWDE 1105	0.260 - 0.291 [6.60 - 7.39]	9/32 (7W)	5	BLUE	28 [711]	22.3 [567]	1.000 [25.40]	8950 [39.8]	PRESENT	50			
FWDE 1106	0.292 - 0.336 [7.41 - 8.53]	5/16 (3W or 7W)	5	BLACK	31 [787]	25.4 [646]	1.063 [27.00]	11200 [49.8]	PRESENT	50			
FWDE 1107	0.337 - 0.394 [8.56 - 10.00]	3/8 (3W or 7W)	6	ORANGE	35 [889]	28.9 [735]	1.063 [27.00]	15400 [68.5]	PRESENT	50			
FWDE 1108	0.395 - 0.474 [10.03 - 12.04]	7/16 (7W)	6	GREEN	38 [965]	30.9 [785]	1.125 [28.58]	20800 [92.5]	PRESENT	25			
FWDE 2115	0.475 - 0.515 [12.06 - 13.08]	1/2 (7W or 19W)	5	BLUE	49 [1245]	40.5 [1029]	1.188 [30.18]	26900 [119.7]	NOT PRESENT	20			
FWDE 2116	0.516 - 0.570 [13.10 - 14.47]	9/16 (7W or 19W)	6	YELLOW	55 [1397]	45 [1143]	1.188 [30.18]	35000 [155.7]	NOT PRESENT	10			
FWDE 1104LA	0.231 - 0.259 [5.86 - 6.57]	1/4 (3W or 7W)	4	YELLOW	25 [635]	20.6 [524]	1.000 [25.40]	6650 [29.6]	PRESENT	100			



- NOTES:
- ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [KN], TORQUE IN. LBS. [N.M], & WEIGHT LBS. [KG].
 - RATINGS:
 - ALL GUY WIRE DEAD-ENDS MEET 100% OF THE WIRE RATED BREAKING STRENGTH (RBS) AS SHOWN IN TABLE 1
 - CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:
 - WIRE - EHS STEEL, ZINC-PLATED TO COVER CLASS "B" COATING PER ASTM A641.
 - SUFFIXES & VARIANT CONFIGURATION:
 - "C"- FOR CLASS "C" COATING, ADD C SUFFIX.
 - "LA"- FOR FWDE1104LA, LA SUFFIX DENOTES CLASS "A" COATING.
 - HAND LAY STANDARD DIRECTION: LEFT

79075	07/02/19	RG	RG	HPS.	HUBBELL® POWER SYSTEMS <small>POWER SYSTEMS, INC.</small>							
EC #	DATE	CHG BY	RESP ENG									
DESC OF DWG: REDRAWN IN INVENTOR NEW CC-TEMPLATE				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS	TITLE FWDE FORMED WIRE DEADENDS							
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:					<table border="1"> <tr> <td>SIZE</td> <td>DWG NO.</td> <td>CAT / PART / ASSY NO.</td> <td>REV</td> </tr> <tr> <td>C</td> <td>CC-17839</td> <td>SEE CHART</td> <td>13</td> </tr> </table>	SIZE	DWG NO.	CAT / PART / ASSY NO.	REV	C	CC-17839	SEE CHART
SIZE	DWG NO.	CAT / PART / ASSY NO.	REV									
C	CC-17839	SEE CHART	13									
DO NOT SCALE THIS DRAWING		DRN BY	BAN	DATE	08/18/05	SHEET	1 OF 1					