




CATALOG NO.	THROAT TYPE	CABLE DIA. RANGE MIN. - MAX.	DIM A	COLOR CODE	WEIGHT	STANDARD PACK
GJ602FC	"C" NECK	0.407 - 0.561 [10.36] - [14.28]	2 [50.80]	GREEN	.320 [.15]	100
GJ603FC	"C" NECK	0.562 - 0.717 [14.30] - [18.25]	2 [50.80]	BLUE	.330 [.15]	100
GJ604FC	"C" NECK	0.718 - 0.919 [18.27] - [23.39]	2 [50.80]	ORANGE	.380 [.17]	75
GJ605FC	"C" NECK	0.920 - 1.125 [23.41] - [28.63]	2 [50.80]	RED	.400 [.18]	75
GJ611FC	"F" NECK	0.250 - 0.406 [6.36] - [10.33]	2.62 [66.55]	WHITE	.330 [.15]	75
GJ612FC	"F" NECK	0.407 - 0.561 [10.36] - [14.28]	2.62 [66.55]	GREEN	.370 [.17]	75
GJ613FC	"F" NECK	0.562 - 0.717 [14.30] - [18.25]	2.62 [66.55]	BLUE	.370 [.17]	75
GJ614FC	"F" NECK	0.718 - 0.919 [18.27] - [23.39]	2.62 [66.55]	ORANGE	.370 [.17]	75
GJ615FC	"F" NECK	0.920 - 1.125 [23.41] - [28.63]	2.62 [66.55]	RED	.460 [.21]	50
GJ616FC	"F" NECK	1.260 - 1.500 [28.66] - [38.18]	2.62 [66.55]	BLACK	.480 [.22]	75
GJ623FC	"J" NECK	0.562 - 0.717 [14.30] - [18.25]	3.25 [82.55]	BLUE	.330 [.14]	75
GJ625FC	"J" NECK	0.920 - 1.125 [23.41] - [28.63]	3.25 [82.55]	RED	.400 [.18]	75
GJ632FC	"K" NECK	0.407 - 0.561 [10.36] - [14.28]	3.87 [98.30]	GREEN	.330 [.15]	75
GJ633FC	"K" NECK	0.562 - 0.717 [14.30] - [18.25]	3.87 [98.30]	BLUE	.380 [.17]	75
GJ635FC	"K" NECK	0.920 - 1.125 [23.41] - [28.63]	3.87 [98.30]	RED	.480 [.22]	75
GJ636FC	"K" NECK	1.130 - 1.500 [28.702] - [38.10]	3.87 [98.30]	BLACK	.560 [.25]	75

ITEM	DESCRIPTION	MATERIAL
1	TIE	PVC CORE COMPOSITE COVER



- NOTES:
1. ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG].
  2. RATINGS:  
A. NA
  3. CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:  
A. UV STABILIZED - MIN. 2.5% CARBON BLACK FILLED BY WEIGHT
  4. SUFFIXS & VARIANT CONFIGURATION:  
A. NA

80142	10/04/19	RG	RG	HPS.	 <b>HUBBELL® POWER SYSTEMS</b> <small>POWER SYSTEMS, INC.</small>			
EC #	DATE	CHG BY	RESP ENG					
DESC OF DWG: REDRAWN IN INVENTOR NEW CC DRAWING TEMPLATE				CONFIDENTIAL: THIS DRAWING AND ITS CONTACTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS	TITLE <b>GJ600, FORMED WIRE COMPOSITE TOP TIE</b>			
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:					<table border="1"> <tr> <td>SIZE <b>C</b></td> <td>DWG NO. <b>CC-19392</b></td> <td>CAT / PART / ASSY NO. <b>SEE TABLE</b></td> <td>REV <b>01</b></td> </tr> </table>	SIZE <b>C</b>	DWG NO. <b>CC-19392</b>	CAT / PART / ASSY NO. <b>SEE TABLE</b>
SIZE <b>C</b>	DWG NO. <b>CC-19392</b>	CAT / PART / ASSY NO. <b>SEE TABLE</b>	REV <b>01</b>					
DO NOT SCALE THIS DRAWING		DRN BY <b>JAT</b>	DATE <b>02/03/1997</b>	SHEET <b>1 OF 1</b>				