


**NOTES:**

1. THIS EXTENSION IS RATED FOR ANSI/SCTE 77 TIER 15 APPLICATIONS.
2. FURNISHED W/(8) 1/2-13 UNC X 5 [203] LONG ZP HEX HEAD BOLTS, (12) ø1/2 [13] ZP FLAT WASHERS, & (6) 1/2-13 UNC ZP HEX NUTS.

DIMENSIONS ARE IN INCHES OR MILLIMETERS IN BRACKETS UNLESS OTHERWISE NOTED.						
DRN	BY	DATE	WEIGHT	 3621 INDUSTRIAL PARK DR LENOIR CITY, TN 37771 800-346-3062 www.quazite.com	LOC	
			240# 109kg		LC	
CHK			SCALE	DRAWING DESCRIPTION <b>QUAZITE® 48 X 72 X 12 EXTENSION</b> <b>INTEGRAL BOTTOM</b> <b>STANDARD VERSION</b>	REV	
ENG			NTS		<b>A</b>	
APR			SIZE			
APR			B			4/13
PROJECT NUMBER					DRAWING NUMBER	
					E0B487212B	
				SHEET 1 OF 1		