



LINE TERMINAL DETAIL



HDG 4-HOLE TERMINAL PAD, PART No. 274914-4002
TWO TIN-PLATED TERMINALS, PART No. TLS89TP
SUITABLE FOR COPPER OR ALUMINUM CONDUCTOR SIZE
Ø 9.3 (.36) - Ø 29 (1.1)
67.4 - 507 sq mm
2/0 - 1000 MCM

GROUND TERMINAL DETAIL



HDG TERMINAL BRACKET, PART No. 89606-4001
ONE HDG TERMINAL, PART No. 271414-3001
SUITABLE FOR COPPER OR ALUMINUM CONDUCTOR SIZE
Ø 7 (.25) - Ø 21 (.81)
25 - 240 sq mm
AWG#4 - 500 MCM
Ø = DIAMETER
HDG = HOT DIP GALVANIZED

CHARACTERISTICS

RATED VOLTAGE (Ur)	6 kVrms
MCOV (Uc)	5.1 kVrms
MASS	5.7 kg (12.6 lb)
COG ABOVE BASE	127 (5)
CREEPAGE DISTANCE	498 (19.6)
STRIKE DISTANCE	175 (6.9)
LIGHTNING IMP W/S	101 kVpk
SWITCHING IMP WET W/S	84 kVpk
POWER FREQ WET W/S	50 kVrms
TOV 1s NO PRIOR DUTY	7.25 kVrms
TOV 10s NO PRIOR DUTY	6.94 kVrms
TOV 1s W/PRIOR DUTY	6.91 kVrms
TOV 10s W/PRIOR DUTY	6.52 kVrms

CANTILEVER FORCE

MAXIMUM CONTINUOUS	3383 N (761 lbf)
ULTIMATE (max pk)	6766 N (1521 lbf)

RECOMMENDED CLEARANCE (METAL - METAL)

PHASE TO GROUND	25.4 (1)
PHASE TO PHASE	50.8 (2)

- NOTES:
1. DIMENSIONS IN millimeters(inches) SUBJECT TO ±3% TOLERANCE
2. CLEARANCE AND INSULATION W/S VOLTAGE APPLY AT SEA LEVEL
3. ARRESTER SUITABLE FOR OPERATION AT ALTITUDES UP TO 4380 m (14370 ft)
4. PACKAGED IN A WOOD CRATE.

.5μSEC 10kA IR kV	SWITCHING SURGE IR kV		MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
	500 A	1 KA	1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
18.6	12.0	12.5	12.8	13.5	14.1	15.2	16.4	18.7

IEEE C62.11

STATION-CLASS
SURGE ARRESTER

Program Revision
2015.07.30.08.09.10

REV DATE
05/03/11

CONFIDENTIAL: THIS DRAWING AND ITS
CONTENTS ARE CONFIDENTIAL AND THE
EXCLUSIVE PROPERTY OF HUBBELL
POWER SYSTEMS. NO PUBLICATION,
DISTRIBUTION OR COPIES MAY BE MADE
WITHOUT THE WRITTEN CONSENT OF
HUBBELL POWER SYSTEMS.
HUBBELL POWER SYSTEMS UNPUBLISHED
ALL RIGHTS RESERVED UNDER THE
COPYRIGHT LAWS.

TITLE

**EVP ARRESTER
5.1 KV MCOV**

SIZE	DWG NO.	CAT / PART / ASSY NO.	REV
S	191054446	EVP0005003008	1
DO NOT SCALE THIS DRAWING	DRN BY	NON	DATE 05/03/11
			SHEET 1 OF 1



HUBBELL® POWER SYSTEMS