



ITEM NO.	DESCRIPTION	QTY.
1	LC CONNECTOR DUST CAP	4
2	LC DUPLEX CONNECTOR BODY	4
3	1.6mm LC CONNECTOR BODY	4
4	1.6mm DUPLEX CABLE	A/R

CATALOG NO.	DESCRIPTION	LENGTH	CABLE JACKET COLOR	CONNECTOR HOUSING COLOR
DFRGLC02XMM	MULTIMODE LC-LC DUPLEX OM3 62.5/125um CORD	**	ORANGE	BEIGE

** AVAILABLE IN 1 METER INCREMENTS UP TO 10 FEET IN LENGTH. REPLACE 'X' IN THE CATALOG NUMBER WITH APPROPRIATE NUMERICAL LENGTH WHEN ORDERING.



- NOTES:
1. CONNECTOR OPTICAL, MECHANICAL, AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
 2. CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
 3. CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
 4. OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
 5. CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
 6. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ENR	DATE	DESCRIPTION	CHK BY	APP BY
A	18104	3/5/13	INITIAL RELEASE	DMP	

Created on AUTOCAD

DESIGNATION AND TOLERANCE FOR MATERIALS SPECIFIED IN THIS DRAWING SHALL BE AS SHOWN IN THE DRAWING UNLESS OTHERWISE SPECIFIED. (SEE HUBBELL DRAWING SPECIFICATIONS FOR TOLERANCES.)
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES AND DECIMAL FRACTIONS THEREOF.
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS AND DECIMAL FRACTIONS THEREOF.
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS AND DECIMAL FRACTIONS THEREOF.
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS AND DECIMAL FRACTIONS THEREOF.

PROJECT REFERENCES

HUBBELL

DRAWN BY: J. RECK
 CHECKED BY:
 APPROVED BY:

DATE: 3/5/13

TITLE: ASSEY MULTIMODE LC-LC DUPLEX 62.5/125 FIBER CORDS

HUBBELL PREMIERE WIRING
 HUBBELL (INCORPORATED) (Delaware)
 14 Lord's Hill Road, Sterling, Connecticut 06398

SIZE: DRAWING NO. HWS14272C
 SCALE: 1/1

SHEET 1 OF 1

REV. A