



HDG 4-HOLE TERMINAL PAD, PART No. 274914-4002



HDG 4-HOLE TERMINAL PAD, PART No. 274914-4001

Ø = DIAMETER
HDG = HOT DIP GALVANIZED

CHARACTERISTICS	
RATED VOLTAGE (Ur)	72 kVrms
MCOV (Uc)	57 kVrms
MASS	18.6 kg (41.1 lb)
COG ABOVE BASE	406 (16)
CREEPAGE DISTANCE	2093 (82.4)
STRIKE DISTANCE	734 (28.9)
LIGHTNING IMP W/S	421 kVpk
SWITCHING IMP WET W/S	353 kVpk
POWER FREQ WET W/S	194 kVrms
TOV 1s NO PRIOR DUTY	82.8 kVrms
TOV 10s NO PRIOR DUTY	79.3 kVrms
TOV 1s W/PRIOR DUTY	79 kVrms
TOV 10s W/PRIOR DUTY	74.6 kVrms

CANTILEVER FORCE	
MAXIMUM CONTINUOUS	1265 N (284 lbf)
ULTIMATE (max pk)	2531 N (569 lbf)

RECOMMENDED CLEARANCE (METAL - METAL)	
PHASE TO GROUND	319.7 (12.6)
PHASE TO PHASE	375.1 (14.8)

- NOTES:
 1. DIMENSIONS IN millimeters(inches) SUBJECT TO ±3% TOLERANCE
 2. CLEARANCE AND INSULATION W/S VOLTAGE APPLY AT SEA LEVEL
 3. ARRESTER SUITABLE FOR OPERATION AT ALTITUDES UP TO 4380 m (14370 ft)
 4. PACKAGED IN A CORRUGATED BOX.

.5μSEC 10kA IR kV	SWITCHING SURGE IR kV		MAXIMUM 8/20 DISCHARGE VOLTAGE - kV AT					
	500 A	1 KA	1.5 kA	3.0 kA	5 kA	10 kA	20 kA	40 kA
192	137	143	147	154	161	173	187	214

IEEE C62.11

STATION-CLASS
SURGE ARRESTER

Program Revision
2015.07.30.08.09.10

REV DATE
05/03/11

CONFIDENTIAL: THIS DRAWING AND ITS
CONTENTS ARE CONFIDENTIAL AND THE
EXCLUSIVE PROPERTY OF HUBBELL
POWER SYSTEMS. NO PUBLICATION,
DISTRIBUTION OR COPIES MAY BE MADE
WITHOUT THE WRITTEN CONSENT OF
HUBBELL POWER SYSTEMS.
HUBBELL POWER SYSTEMS UNPUBLISHED
ALL RIGHTS RESERVED UNDER THE
COPYRIGHT LAWS.

TITLE

**EVP ARRESTER
57 KV MCOV**

SIZE
S

DWG NO.
191064519

CAT / PART / ASSY NO.
EVP0057003012

REV
1

DO NOT SCALE
THIS DRAWING

DRN BY
NON

DATE
05/03/11

SHEET
1 OF 1



HUBBELL POWER SYSTEMS