





ITEM NO.	DESCRIPTION	QTY.
1	LC DUPLEX ADAPTER	8
2	LC DUPLEX DUST CAPS (INSTALLED)	32
3	SCREW, ADAPTER MOUNTING	16
4	NYLATCH PUSH/PULL FASTENER	2
5	ADAPTER PLATE, 8 PORT	1

CATALOG NUMBER	DESCRIPTION
FSPLCDx8y	LOADED FSP PANEL W/8 LC DUPLEX ADAPTERS

CATALOG NUMBER LEGEND:

"x":
M - MULTIMODE, PHOS-BR SLEEVE
S - SINGLEMODE, ZIRCONIA SLEEVE

"y":
AQ - AQUA
BE - BEIGE
BK - BLACK
B - BLUE
GN - GREEN
R - RED
Y - YELLOW



NOTES:

- SUPPLIED WITH PUSH/PULL FASTENER FOR EASY INSTALLATION/REMOVAL.
- PANELS FIT INTO HUBBELL WALL MOUNT AND RACK MOUNT CABINETS.
- BLACK ELECTROSTATICALLY APPLIED POWDER COAT.
- ADAPTERS SUPPLIED WITH DUST CAPS INSTALLED.
- SPLIT SLEEVE MATERIAL- SEE TABLE ZIRCONIA COMPATIBLE WITH BOTH SINGLEMODE AND MULTIMODE FIBER PHOSPHOR BRONZE COMPATIBLE WITH MULTIMODE FIBER ONLY
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
C	17866	05/08/12	UPDATED CAT. NUMBER LIST	MMA	

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM).

TOLERANCES
.xx = ±.01 (.25)
.xxx = ±.005 (.127)
.xxxx = ±.0025 (.0635)
ANGLE TOL .±1°

PROJECT REFERENCE:
051-08

MATERIAL:
SEE TABLE

DRAWN BY:
C. DUSSAULT 10/22/08

CHECKED BY:

APPROVED BY:

HUBBELL
Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE:
FIBER ADAPTER PANEL
HIGH DENSITY - 8 PORT
WITH LC DUPLEX ADAPTERS

SIZE: C
DRAWING NO.: HWS12728C
SCALE: N/A

REV.: C