






ITEM NO.	DESCRIPTION	QTY.
1	FINGER GUARD W/BARBS	2
2	57 CFM FAN	2
3	NUT & BOLT WITH RUBBER WASHER	8
4	FAN PANEL, COLD ROLLED STEEL	1
5	2-POLE 6-POSITION TERMINAL BLOCK	1
6	TY-WRAP CORD HOLDER	1

CATALOG NUMBER	DESCRIPTION	PLUG TYPE
HWKF120	114CFM, 120VAC, 60Hz. QUADCAB FAN KIT	NEMA 5-15
HWKF230	114CFM, 230VAC, 50Hz. QUADCAB FAN KIT	CEE 7/7



AIR FLOW →

GROUND STUD FOR FANS:
FANS TO BE INDIVIDUALLY
GROUNDED TO THE PANEL




SEE TABLE FOR PLUG
STYLE

WIRING DIAGRAM

NOTES:

- HARDWARE PACK CONTAINS:
(4) 1/4-20 x 5/8 CARRIAGE BOLT
(4) 1/4-20 LOCKNUT
- SEE INSTRUCTION SHEET 77355201 FOR INSTALLATION INSTRUCTIONS.
- QUADCAB FAN KIT COMES ASSEMBLED.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
B	5346	6/30/04	UPDATED ENTIRE ASSEMBLY	GPE	MMA
A	4819	11/11/02	INITIAL RELEASE	PSM	RB

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .X = ±.03 (.8) .XX = ±.02 (.4) .XXX = ±.010 (.25) ANGLE TOL ±1°		PROJECT REFERENCE:		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:		
	DRAWN BY: PAUL S. MAGUIRE 11/12/02		CHECKED BY: ROB BAXTER 11/20/02		TITLE: CABINETS WALL MOUNT CABINETS ASSY, FAN KIT FOR THE QUADCAB
	APPROVED BY: ROB BAXTER 11/20/02		SIZE D	DRAWING NO. C11685	REV. B
SCALE: NTS		SHEET 1 OF 1			