



6	5	4	3	2	1
CATALOG NUMBER	FIBER DESCRIPTION	SPLIT SLEEVE MAT'L	ADAPT. BODY COLOR	FIBER TYPE	
OCSC50	50/125um MULTIMODE	PHOSPHOR BRONZE	BEIGE	OM2	
OCSC62	62.5/125um MULTIMODE	PHOSPHOR BRONZE	BEIGE	OM1	
OCSCSM	9/125um SINGLEMODE	ZIRCONIA	BLUE	OS2	
OCSC50G	50/125nm ENHANCED MULTIMODE	PHOSPHOR BRONZE	BEIGE	OM3	
OCSC50G4	50/125nm ENHANCED MULTIMODE	PHOSPHOR BRONZE	BEIGE	OM4	



- NOTES
- SUPPLIED WITH PUSH/PULL FASTENERS FOR EASY INSTALLATION/REMOVAL.
 - PANELS FIT INTO HUBBELL WALL MOUNT AND RACK MOUNT CABINETS.
 - FINISH: BLACK POWDER COAT.
 - ADAPTERS SUPPLIED WITH DUST CAPS INSTALLED.
 - FULLY TESTED WITH TEST DATA INCLUDED.
 - 50/125um ENHANCED MULTIMODE FIBER IS RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
 - SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
D	19601	03/16/15	REVISED MATERIAL CALLOUT	MMA	

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .X = ±.03 (.8) .XX = ±.02 (.4) .XXX = ±.010 (.25) ANGLE TOL ±1°		PROJECT REFERENCE:		 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: C.R.S. ENGINEERING THERMOPLASTIC		
			DRAWN BY: PAUL S. MAGUIRE 01/09/03		SIZE: C DRAWING NO. C11882
			CHECKED BY: JON LUTZEN 01/15/03		REV. D
		APPROVED BY: JON LUTZEN 01/15/03		SCALE: 1/1 SHEET 1 OF 1	