

CATALOG NO. OFCLEANER3OZ	DESCRIPTION 3oz CAN OF CLEANER FLUID
-----------------------------	---

NOTES:

1. KIT SHOULD CONTAIN:  
(1) 3oz CLEANING FLUID CAN
2. SDS SHEET AVAILABLE.
3. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.



- High-purity cleaning fluid for fiber optics
- Perfectly cleans all optic components
- Completely removes dust, dirt, fingerprints, moisture and dissipates static
- Cleans in five seconds. Dries instantly
- Safe on all surfaces
- Non-flammable. Non-hazardous. Non-regulated
- Ship anywhere, any way
- Military approved
- Each bottle contains 400+ cleanings

**Technical Details**

Application	High-purity fiber optic cleaning fluid
Dispensing Method	Not pressurized, metered-dose, pump
Appearance	Clear, colorless liquid
Flash point (TCC)	None, not flammable
Transport Classification	Not regulated for transport
NFPA Ratings	Health: 3; Fire: 1; Reactivity: 0

Sticklers® Fiber Optic Splice & Connector Cleaner is the only optical-grade cleaning fluid on the market specifically engineered for fast, reliable and low-cost cleaning of fiber optic network connectors, receptacles and fiber. Use with the Sticklers CleanStix™ connector cleaning sticks or Sticklers CleanWipes™ fiber optic cleaning wipes. Use with any of the "one click" cleaning tools for greatly improved cleaning results.

Packaged in a hermetically-sealed container, this high-purity cleaning fluid removes fingerprints, oils, buffer residues and surface films. It easily removes dust and lint particles by eliminating static charges that attract and "lock" particulate to end-faces. Unlike other cleaners, the Sticklers Fiber Optic Splice & Connector Cleaner displaces moisture and dries quickly. Since it does not contain water, it will never freeze in low ambient temperatures. Because it's fast drying and leaves no residues, it can't be trapped inside alignment sleeves. It's safe on single-mode and multi-mode fiber, plastic optical fiber, glass, adhesives, plastic housings, epoxies and most optical coatings. It also can be used to clean lenses, mirrors, gratings, prisms and displays.

The compact, spill-proof canister comes with the patented Triton™ three way dispenser (see illustration on right), fitting easily in tool kits. Each contains over 400 cleanings. When you need perfectly clean splices and connectors, the Sticklers CleanStix connector cleaning sticks and the Sticklers Fiber Optic Splice & Connector Cleaner is your key to fast, reliable, and low cost cleaning.

This fiber optic cleaner is ideal for factory volume production as well as commercial and military tool kit uses. The Sticklers Fiber Optic Splice & Connector Cleaner is factory packaged in a hermetically sealed non-pressurized container. It is non-flammable, non-hazardous and can be transported anywhere in the world by ground, air or ocean without hazmat markings or fees. Larger package sizes available; contact your Sticklers distributor for details.

**Triton Three-Way Dispensing**



- 1) Flush out receptacles and connectors.
- 2) Dampen Sticklers CleanStix connector cleaning sticks or any "one-click" tool.
- 3) Dampen Sticklers CleanWipes fiber optic cleaning wipes for splicing or cleaning connector endfaces.

1	21320	09/09/15	INITIAL RELEASE	MMA	
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on INVENTOR	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: NPD-00162		<b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355		
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:  SEE NOTES			TITLE: FIBER CLEANING FLUID, NON-HAZ	
			DRAWN BY: MABBY 08/17/15		SIZE: <b>C</b>	DRAWING NO.: <b>HWS14535C</b>	REV.: <b>1</b>
			CHECKED BY:		SCALE: N/A SHEET 1 OF 1		
		APPROVED BY:					