

NOTES:

1. ALL GUY WIRE DEAD-ENDS MEET 100% OF THE WIRE RATED BREAKING STRENGTH (RBS) AS SHOWN IN TABLE 1.
2. B-COAT OR C-COAT GALVANIZING-ASTM SPECIFICATION A641. B-COAT IS STANDARD
3. NO SECOND COLOR MARK
4. HAND LAY STANDARD DIRECTION: LEFT
5. ALL DIMENSIONS FOR REFERENCE ONLY





TABLE 1

CATALOG NO.	1	2	3	No. of Wires	COLOR	STRAND SIZE & CONSTRUCTION	APPLICATION	RBS (POUNDS)	NOTE	SECOND COLOR MARK
FWDE1104TE	25	0.75	1.0000	5	YELLOW	1/4 (3W or 7W)	0.231 TO 0.259 in (5.867 TO 6.579 mm) EHS STEEL STRAND	6650	DET. A	
FWDE1106TE	31	0.75	1.0625	5	BLACK	5/16 (3W or 7W)	0.292 TO 0.336 in (7.417 TO 8.534 mm) EHS STEEL STRAND	11200	DET. A	
FWDE1107TE	35	0.75	1.0625	6	ORANGE	3/8 (3W or 7W)	0.337 TO 0.394 in (8.560 TO 10.008 mm) EHS STEEL STRAND	15400	DET. B	
FWDE1108TE	38	1.00	1.1250	6	GREEN	7/16 (7W)	0.395 TO 0.474 in (10.033 TO 12.040 mm) EHS STEEL STRAND	20800	DET. B	
FWDE2115TE	49	1.00	1.1875	5	BLUE	1/2 (7W or 19W)	0.475 TO 0.515 in (12.065 TO 13.081 mm) EHS STEEL STRAND	26900	DET. B	NOTE 3
FWDE2116TE	55	1.00	1.1875	6	YELLOW	9/16 (7W or 19W)	0.516 TO 0.570 in (13.106 TO 14.478 mm) EHS STEEL STRAND	35000	DET. B	NOTE 3

68329	01/31/2017	RG	RG	FARGO TOLERANCE CHART	HUBBELL POWER SYSTEMS
EC #	DATE	CHG BY	RESP ENG		
DESC OF DWG: ADDED COLUMN 'NO. OF WIRES'. -- -- REASON (S) FOR CHANGE: DISPOSITION OF MAT'L: --				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED. ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS.	TITLE CUSTOMER DWG. FWDE - TAPERED END
DO NOT SCALE THIS DRAWING		DRN BY BAF	DATE 03/10/06	SIZE B	DWG NO. CC-17956
				CAT / PART / ASSY NO. SEE CHART	REV 06
				SHEET 1 OF 1	