

CATALOG NUMBER	TRADE NAME	DESC/SIZE	SERVICE TEMP.	GRIT TYPE	TO BE USED ON			COLOR	APPROX. WT. EACH LB. [KG]	STANDARD PACK
					COMPRESSION	GROOVE/BOLTED	PAD			
VS8HTJC	ANDERSON	8 OZ. PLASTIC BOTTLE	-40°F to +480°F (-40°C to 250°C)	FINE CONDUCTIVE	•	•	•	GRAY	.84 [0.380]	12
HTJC16	FARGO	CAULK TUBE	-40°F to +480°F (-40°C to 250°C)	FINE CONDUCTIVE	•	•	•	GRAY	1.00 [0.454]	25
HTJCNG4B	ANDERSON	4 OZ. PLASTIC BOTTLE	-40°F to +400°F (-40°C to 200°C)	NON GRITTED		•	•	AMBER	.38 [0.172]	24
HTJCNG8B	ANDERSON	8 OZ. PLASTIC BOTTLE	-40°F to +400°F (-40°C to 200°C)	NON GRITTED		•	•	AMBER	.50 [.227]	18
HTJCNGQC	ANDERSON	QUART CAN	-40°F to +400°F (-40°C to 200°C)	NON GRITTED		•	•	AMBER	2.00 [.907]	6

ITEM	DESCRIPTION	MATERIAL
1	INHIBITOR CONTAINER	-
2	CONTAINER CAP WITH FILLER NOZZLE	-
3	NOZZLE CAP	-



- NOTES:
- ALL DIMENSIONS FOR REFERENCE ONLY. DISTANCE IN. [MM], FORCE LBS. [kN], TORQUE IN. LBS. [N.m], & WEIGHT LBS. [KG].
  - RATINGS:  
A. NA
  - CERTIFICATIONS, SPECIFICATIONS, & STANDARDS:  
A. NA
  - SUFFIXES & VARIANT CONFIGURATION:  
A. NA

79522	08/14/19	RG	RG	HPS.	<b>HUBBELL® POWER SYSTEMS</b> POWER SYSTEMS, INC.
EC #	DATE	CHG BY	RESP ENG		
DESC OF DWG: INITIAL RELEASE				CONFIDENTIAL: THIS DRAWING AND ITS CONTENTS ARE CONFIDENTIAL AND THE EXCLUSIVE PROPERTY OF HUBBELL POWER SYSTEMS. NO PUBLICATION, DISTRIBUTION OR COPIES MAY BE MADE WITHOUT THE WRITTEN CONSENT OF HUBBELL POWER SYSTEMS. HUBBELL POWER SYSTEMS UNPUBLISHED ALL RIGHTS RESERVED UNDER THE COPYRIGHT LAWS	TITLE <b>HTJC, ELECTRICAL JOINT COMPOUND/INHIBITOR</b>
REASON (S) FOR CHANGE: DISPOSITION OF MAT'L:					SIZE <b>C</b> DWG NO. <b>CC-26298</b> CAT / PART / ASSY NO. <b>SEE TABLE</b> REV <b>00</b>
				DO NOT SCALE THIS DRAWING	DRN BY <b>RG</b> DATE <b>08/06/2019</b> SHEET <b>1 OF 1</b>