


NOTE:

1. Applicable cables : Copper cable
2. Dia.5.0mm -150sq.mm
3. ACSR
4. Don't use for ACSR withPRURAL reinforced steelwires.
5. 25sq.mm-200sq.mmBigger mouth open size (34 mm)

-	-	-	-	TOLERANCE CHART 0.0 = ±0.10 0.00 = ±0.02 0.000 = ±0.005 ANGLE = ±0.5°	<div> HUBBELL POWER SYSTEMS, Inc.</div>			
EC #	DATE	CHG BY	RESP ENG		TITLE Hot Stick type cable cutter			
DESC OF DWG: - -  								