


NEMA NO.	RATING	POLE/WIRE	CAT. NO.	CONTACTS CONFIGURATION	VOLTAGE COLOR CODE
L5-30R	125V	2P/3W GROUNDING	HBL2613ST		YELLOW
L6-30R	250V	2P/3W GROUNDING	HBL2623ST		BLUE

NOTES (UNLESS OTHERWISE SPECIFIED):

- 1. DIMENSIONS ARE IN INCHES [mm].
- 2. ALL DEVICES ARE cULus LISTED & FED SPEC.
- 3. CORD TYPES: S & SJ, ROUND CORD ONLY
- 4.WIRE TERMINAL ACCOMODATION: 14AWG 8AWG STRANDED COPPER WIRE ONLY
- 5. CONDUCTOR STRIP LENGTH: 3/4" (19mm).
- 6. ASSEMBLY SCREWS ARE PHILLIPS/SLOTTED/ROBERTSON HEAD.
- 7. CATALOG NUMBERS & RATING ARE PAD PRINTED ON THE SIDE OF THE DEVICE, COLOR CODED BY VOLTAGE.

LIST OF PARTS					
DESCRIPTION	MATERIAL	FINISH)IME		
CONTACT BODY	NYLON	NATURAL	NSI		
COVER	NYLON	BLACK	SNC		
CORD CLAMP	NYLON	NATURAL	苗		
CONTACTS	COPPER ALLOY		SEE		
RETAINER	NYLON	BLACK	\circ		
SPRING	STAINLESS STEEL		I AT		
PLUNGER	NYLON		AT. NO. TABLE		
ASSEMBLY	STEEL	ZINC PLATE]'''		
FASTENERS	SIEEL	ZINCPLATE			
CORD CLAMP	NYLON	BLACK			
INSERTS	INTLOIN	DLACK			
ISOLATOR	NYLON	BLACK			
DUST SHIELD	TPE	BLACK			



CAT. NO. HBL2613ST (NOT SHOWN TO SCALE)

1	INITIAL RELEASE PER DCN	RGP	2/22/22	1
	220304017679 AM			L
REV	DESCRIPTION	APP	DATE	

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE

3-WIRE SCREWLESS TERMINATION CONNECTOR



WIRING DEVICE-KELLEMS **HUBBELL INCORPORATED** SHELTON, CT

M-14327

TOLERANCES UNLESS
OTHERWISE SPECIFIED
.XX = ± .01
.XXX= ± .005
ANGLE TOL. ±2' ΑM 1:1 DATE 2/22/22 CHK. BY RGP

CAGE CODE 74545