




ITEM NO.	DESCRIPTION	QTY.
1	FC CONNECTOR DUST CAP	4
2	FC CONNECTOR NUT	4
3	2.0mm FC CONNECTOR BOOT	4
4	2.0mm DUPLEX CABLE	A/R

CATALOG NO.	DESCRIPTION	CABLE TYPE	CABLE JACKET COLOR
DFPCFCFCxxSM	FIBER OPTIC PATCHCORD, PLENUM, SINGLEMODE, FC-FC DUPLEX, xx* METER	9/125 OS2	YELLOW

xx* MEANS AVAILABLE IN THE FOLLOWING LENGTHS:


- 1 METER
- 2 METER
- 3 METER
- 4 METER
- 5 METER
- 10 METER



NOTES:

1. CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA 568-C.3 SPECIFICATIONS.
2. CONNECTOR USES A UPC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
3. CONNECTOR NUT IS NICKEL PLATED ZINC DIE CAST.
4. OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
5. CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
6. POLARITY: A TO B PER TIA-568.3.
7. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	21494	9/13/16	UPDATED TABLE	JJRJ	MMA

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: 053-12	 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378	
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:		TITLE: FIBER PATCH CORDS ASSY, SINGLEMODE FC-FC DUPLEX 9/125
	DRAWN BY: C. GRIBBLE 8/1/12		CHECKED BY:	SIZE: D	DRAWING NO. HWS14100C
	APPROVED BY:		SCALE: 1/1	SHEET 1 OF 1	REV. 2