




M-14686

1




CAT NO.	NEMA NO.	RATING	POLE/WIRE	CONFIGURATION	RATING RING COLOR
IG2610ST	L5-30	30A 125V	2P/3W GROUNDING		YELLOW
IG2620ST	L6-30	30A 250V	2P/3W GROUNDING		BLUE

- NOTES:
- DIMENSIONS ARE IN INCHES [mm].
 - WIRING TERMINAL ACCOMMODATION:
 - SOLID WIRE: 14 AWG - 10 AWG COPPER WIRE ONLY
 - STRANDED WIRE (INCLUDING COMPACT STRANDED): 14 AWG - 8 AWG COPPER WIRE ONLY
 - CONDUCTOR STRIP LENGTH: 0.600" (15.24mm)

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER	THERMOPLASTIC	
MID HOUSING	THERMOPLASTIC	
BASE	THERMOPLASTIC	
CONTACTS	BRASS	
SPRING	STEEL	
PLUNGER	THERMOPLASTIC	
GR. SHUNT	BRASS	
MOUNTING PLATE	BRASS	
RIVET	BRASS	
INSULATOR	THERMOPLASTIC	

1	INITIAL RELEASE PER DCN 230802032315 AMS	DL	8/3/23
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].			
TITLE: CUST. DWG, 30A 3 WIRE ISOLATED GROUND SPRING TERMINATION RECEPTACLE			
 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°		DR. BY AMS CHK. BY DL	SCALE 1 : 1 DATE 6/29/23