


ITEM NO.	DESCRIPTION	QTY.
1	LC CONNECTOR DUST CAP	2
2	LC DUPLEX CONNECTOR BODY	1
3	2.0mm LC CONNECTOR BOOT	2
4	2.0mm DUPLEX CABLE	A/R
5	2.0mm ST CONNECTOR BOOT	2
6	ST CONNECTOR NUT	2
7	ST CONNECTOR DUST CAP	2

CATALOG NO	DESCRIPTION	FIBER TYPE	CABLE COLOR
DFPCLCSTSxxSM	FIBER OPTIC PATCHCORD, PLENUM, SINGLEMODE, LC-ST, xx* METER	9/125 OS2	YELLOW

**xx\* MEANS AVAILABLE IN THE FOLLOWING LENGTHS:**

1 METER  
2 METER  
3 METER  
4 METER  
5 METER  
10 METER



- NOTES:
1. CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-B.3 SPECIFICATIONS.
  2. CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
  3. LC CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN. ST CONNECTOR NUT IS NICKEL PLATED ZINC DIECAST.
  4. OPTICAL INSERTION LOSS AND RETURN LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
  5. CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
  6. POLARITY: A TO B PER TIA-568.3
  7. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
D	21494	09/12/16	UPDATED TABLE	JJRJ	MMA

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°	PROJECT REFERENCE:	<b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION	MATERIAL:	
DRAWN BY: PAUL S. MAGUIRE 02/25/03		CHECKED BY: CINDY TALBOT 04/24/03	SIZE: <b>D</b>
APPROVED BY: CINDY TALBOT 04/24/03		DRAWING NO.: <b>C11355</b>	REV. <b>D</b>
SCALE: 1/1		SHEET 1 OF 1	