




1



15A/125V



CATALOG NO: BR15STWR	CATALOG NO: BR20STWR
NOT SHOWN TO SCALE	NOT SHOWN TO SCALE

HUBBELL CATALOG NUMBERS

AMPERAGE	BLACK	BLUE	BROWN	GRAY	IVORY	LT. ALMOND	RED	WHITE	GREEN	ORANGE
15A	BR15STBKWR	BR15STBLWR	BR15STWR	BR15STGYWR	BR15STIWR	BR15STLAWR	BR15STRWR	BR15STWWR	BR15STGNWR	BR15STOWR
20A	BR20STBKWR	BR20STBLWR	BR20STWR	BR20STGYWR	BR20STIWR	BR20STLAWR	BR20STRWR	BR20STWWR	BR20STGNWR	BR20STOWR

GENERAL NOTES:

1. DIMENSIONS ARE IN INCHES [MM].
2. ALL DEVICES UL LISTED, CSA & FED. SPEC. CERTIFIED
3. TERMINALS ACCOMMODATE #14 - #10 AWG COPPER WIRE ONLY.

CAGE CODE 74545

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
TOP COVER	PC (f1)	-
BASE	PC	-
BRIDGE	.04 GALV. STL.	-
GROUND CONTACTS	COPPER ALLOY	-
LINE CONTACTS	COPPER ALLOY	-
REAR COVER	PC	-
PLUNGER	NYLON	-
SPRING	STAINLESS STEEL	-
STAPLE	STAINLESS STEEL	-
WASHER	PVC FILM	BLACK
GROUND STRAP	COPPER ALLOY	-
MOUNTING SCREW	STAINLESS STEEL	PASSIVATE

DIMENSION SHEET FOR CAT. NO.
SEE TABLE

३।

M-14697

7

1	INITIAL RELEASE PER DCN 231120034858 WHD DSL	WHD	11/17/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.
DIMENSIONS ARE IN INCHES [mm].

TITLE

WR DUPLEX RECEPTACLE, EdgeConnect,
15A & 20A, COMMERCIAL



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY	WHD	SCALE	1 : 1
	CHK. BY	DSL	DATE	11/13/23