






NOTES UNLESS OTHERWISE SPECIFIED:

- 1. DIMENSIONS SHOWN ARE IN INCHES [mm].
- 2. ENCLOSURE TYPE 4X, 12.
- 3. cULus LISTED.
- 4. NSF CERTIFIED AND IP69k RATING.

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
COVER & BASE	PBT	
SHAFT ADAPTER	PBT	
HANDLE	PBT	
(4) COVER SCREWS	ST.STEEL	
GASKET COVER	NITRILE RUBBER	
JOG SW.	POLYAMIDE	
CONDUIT HUB	ZINC	
MOUNTING FEET	PBT	



CATALOG NO. HBLDS30J
(NOT SHOWN TO SCALE)

2	REVISED. CAT. NO.'s PER DCN 240326038044 CAC		03/26/24
1	NEW RELEASE PER DCN 230711031802 CAC		07/24/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

CATALOG NO. HBLDS30J
30 AMP 600V A.C. RATINGS

HP	VOLTAGE
1 HP	120V AC 1Ø
3 HP	200-240V AC 1Ø
5 HP	480V AC 1Ø
7.5 HP	200-240V AC 3Ø
15 HP	480V AC 3Ø
15 HP	600V AC 3Ø

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY CAC	SCALE 1 / 2
	CHK. BY	DATE 07-24-23