



ITEM NO.	DESCRIPTION	QTY.
1	ST CONNECTOR DUST CAP	4
2	ST CONNECTOR NUT	4
3	1.8mm ST CONNECTOR BOOT	4
4	1.8mm DUPLEX CABLE	A/R

CATALOG NO.	DESCRIPTION	LENGTH	CABLE JACKET
DEPSTST10MM	MULTIMODE ST-ST DUPLEX 62.5/125um PATCH CORD	1 METER	ORANGE
DEPSTST5MM	MULTIMODE ST-ST DUPLEX 62.5/125um PATCH CORD	5 METER	ORANGE
DEPSTST3MM	MULTIMODE ST-ST DUPLEX 62.5/125um PATCH CORD	3 METER	ORANGE
DEPSTST1MM	MULTIMODE ST-ST DUPLEX 62.5/125um PATCH CORD	1 METER	ORANGE
DEPSTST10MM	MULTIMODE ST-ST DUPLEX 62.5/125um PATCH CORD	10 METER	ORANGE



- NOTES:
- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA 568-B.3 SPECIFICATIONS.
 - CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
 - CONNECTOR NUT IS NICKEL PLATED ZINC DIE CAST.
 - OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
 - CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
 - SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ENR	DATE	DESCRIPTION	CHG BY	APPD BY
B	6159	9/27/07	REDUCED CABLE JACKET DIAMETER	CD	

Created on AUTOCAD

DESCRIPTION: FOR USE PER SPECIFICATIONS FOR HUBBELL PREMISE WIRING. THIS DRAWING IS THE PROPERTY OF HUBBELL AND IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. HUBBELL ASSUMES NO LIABILITY FOR THE USE OF THIS DRAWING.

PROJECT REFERENCE: HUBBELL PREMISE WIRING

DRAWN BY: PAUL S. MANIOME 02/12/03

CHECKED ONLY: TILBORT 04/24/03

APPROVED BY: ONLY TILBORT 04/24/03

TITLE: HUBBELL PREMISE WIRING

FILE NO.: HUBBELL PREMISE WIRING

SCALE: 1/1

SHEET: 1 OF 1

REV: B