



M-14824


1



20A/125V
(M1 SHOWN)




20A/125V
(M2 SHOWN)



LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
TOP COVER	PC	-
BASE	PC	-
BRIDGE	.04 GALV. STL.	-
GROUND CONTACTS	COPPER ALLOY	-
LINE CONTACTS	COPPER ALLOY	-
REAR COVER	PC	-
PLUNGER	NYLON	-
GROUND STRAP	COPPER ALLOY	-



CATALOG NO: 5362STM1 CATALOG NO: 53262STM2
(NOT SHOWN TO SCALE) (NOT SHOWN TO SCALE)

1	INITIAL RELEASE PER ECN 240826042054 WHD DSL	WHD	8/26/24
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.
DIMENSIONS ARE IN INCHES [mm].

TITLE HUBBELL PRO DUPLEX RECEPTACLE,
CUSTOM BRIDGES, EdgeConnect,™ 20A
FINDER FACE, FED SPEC



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS
OTHERWISE SPECIFIED
.XX = ± .01
.XXX = ± .005
ANGLE TOL. ±2°

DR. BY SIV
CHK. BY WHD

SCALE 3:4
DATE 08/26/24

HUBBELL CATALOG NUMBERS

CONFIGURATION	BLACK	BLUE	GRAY	WHITE	RED
20A NO EARS	5362STBKM1	5362STBLM1	5362STGYM1	5362STWM1	5362STRM1
20A NO EARS & (2) #6-32 TAPPED HOLES	5362STBKM2	5362STBLM2	5362STGYM2	5362STWM2	5362STRM2

GENERAL NOTES:

- DIMENSIONS ARE IN INCHES [MM].
- ALL DEVICES UL LISTED, CSA & FED. SPEC. CERTIFIED
- TERMINALS ACCOMMODATE #14 - #10 AWG COPPER CONDUCTORS OR UL LISTED CCA CONDUCTORS ONLY