


ITEM NO.	DESCRIPTION	QTY.
1	LC CONNECTOR DUST CAP	2
2	LC DUPLEX CONNECTOR BODY	1
3	LC CONNECTOR BOOT	2
4	DUPLEX CABLE	A/R
5	FC CONNECTOR BOOT	2
6	FC CONNECTOR NUT	2
7	FC CONNECTOR DUST CAP	2

CATALOG NO.	DESCRIPTION	CABLE TYPE	CABLE JACKET COLOR
DFRCLCFCSxxSM	FIBER OPTIC PATCHCORD, RISER, SINGLEMODE, LC-FC DUPLEX, xx* METER	9/125 OS2	YELLOW

xx* MEANS AVAILABLE IN THE FOLLOWING LENGTHS:


- 1 METER
- 2 METER
- 3 METER
- 4 METER
- 5 METER
- 10 METER



NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
- CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
- LC CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN. ST CONNECTOR NUT IS NICKEL PLATED ZINC DIECAST.
- OPTICAL INSERTION LOSS AND RETURN LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
- CABLE MARKINGS TO IDENTIFY CHANNEL (1 OR 2) AND EACH END (A OR B).
- POLARITY: A TO B PER TIA-568.3.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT PRIOR NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	21494	09/08/16	REVISED TABLE	JJRJ	MMA

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: 094-13	 Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 23 CLARA DRIVE, SUITE 103 MYSTIC, CT 06355	
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL:		TITLE: FIBER PATCH CORDS SINGLEMODE LC-FC DUPLEX 9/125
	DRAWN BY: D.O'CONNOR 12/19/13		CHECKED BY:	SIZE: D	DRAWING NO.: HWS14388C
	APPROVED BY:		SCALE: 1/1	SHEET 1 OF 1	REV. 2