


ITEM NO.	DESCRIPTION	QTY.
1	LC CONNECTOR DUST CAP	1
2	LC CONNECTOR BODY	1
3	LC CONNECTOR BOOT	1
4	250um BUFFERED FIBER	A/R



CATALOG NO.	DESCRIPTION	LENGTH	BUNDLE SIZE	HOUSING COLOR	BOOT COLOR
FPBKLTR6LC1M	62.5/125 OM1 MULTIMODE, LC	3 METER	6	BEIGE	BEIGE
FPBKLTR6LC2M	50/125 OM2 MULTIMODE, LC	3 METER	6	BEIGE	BEIGE
FPBKLTR6LC3M	50/125 OM3 MULTIMODE, LC	3 METER	6	AQUA	AQUA
FPBKLTR6LC4M	50/125 OM4 MULTIMODE, LC	3 METER	6	AQUA	AQUA
FPBKLTR6LC6S	9/125 OS2 SINGLEMODE, LC	3 METER	6	BLUE	BLUE
FPBKLTR12LC1M	62.5/125 OM1 MULTIMODE, LC	3 METER	12	BEIGE	BEIGE
FPBKLTR12LC2M	50/125 OM2 MULTIMODE, LC	3 METER	12	BEIGE	BEIGE
FPBKLTR12LC3M	50/125 OM3 MULTIMODE, LC	3 METER	12	AQUA	AQUA
FPBKLTR12LC4M	50/125 OM4 MULTIMODE, LC	3 METER	12	AQUA	AQUA
FPBKLTR12LC6S	9/125 OS2 SINGLEMODE, LC	3 METER	12	BLUE	BLUE

BUFFER TUBE COLORS	12-PACK
6-PACK	BLUE
BLUE	BLUE
ORANGE	ORANGE
GREEN	GREEN
BROWN	BROWN
SLATE	SLATE
WHITE	WHITE
RED	RED
BLACK	BLACK
YELLOW	YELLOW
VIOLET	VIOLET
ROSE	ROSE
AQUA	AQUA


B

NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
- CONNECTOR USES A PC (MULTIMODE) OR UPC (SINGLEMODE) TIP ZIRCONIA CERAMIC FERRULE.
- CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
- OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PIGTAIL.
- 50/125um OM3 MULTIMODE IS CORNING FIBER, RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
- 50/125um OM4 MULTIMODE IS CORNING FIBER, RATED FOR 100Gb/s TRANSMISSION FOR UP TO 150 METERS AT 850nm.

A

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
1	17893	3/20/12	INITIAL RELEASE	CG	



B

NOTES:

- CONNECTOR OPTICAL, MECHANICAL AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATIONS.
- CONNECTOR USES A PC (MULTIMODE) OR UPC (SINGLEMODE) TIP ZIRCONIA CERAMIC FERRULE.
- CONNECTOR HOUSING IS INJECTION MOLDED ENGINEERING PLASTIC RESIN.
- OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PIGTAIL.
- 50/125um OM3 MULTIMODE IS CORNING FIBER, RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
- 50/125um OM4 MULTIMODE IS CORNING FIBER, RATED FOR 100Gb/s TRANSMISSION FOR UP TO 150 METERS AT 850nm.

A

Created on AUTOCAD		DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL ±1°		PROJECT REFERENCE: 2012-003		HUBBELL Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378	
IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: SEE NOTES		DRAWN BY: C. GRIBBLE 3/20/12		TITLE: FIBER PIGTAIL BUNDLES LC SM/MM, COLOR CODED BUFFER	
APPROVED BY:		CHECKED BY:		SIZE: C		DRAWING NO. HWS14048C	
SCALE: 1/1		SHEET 1 OF 1		REV. 1			