


ITEM NO.	DESCRIPTION	QTY.
1	LC DUPLEX CONNECTOR	2
2	LC DUST CAP	4
3	50/125 OM3 CABLE	N/A
1	LC DUPLEX CONNECTOR	2

CATALOG NUMBER	LENGTH (METERS)	DESCRIPTION
HDPCLC50G3M1	1	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M2	2	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M3	3	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M4	4	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M5	5	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M6	6	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M8	8	HIGH DENSITY LC DUPLEX, OM3 FIBER
HDPCLC50G3M10	10	HIGH DENSITY LC DUPLEX, OM3 FIBER



- NOTES:
- CONNECTOR OPTICAL, MECHANICAL, AND ENVIRONMENTAL PERFORMANCE MEETS TIA/EIA-568-C.3 SPECIFICATION.
 - FIBER IS RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
 - CONNECTOR USES A PC RADIUS TIP ZIRCONIA CERAMIC FERRULE.
 - OPTICAL INSERTION LOSS TEST DATA INCLUDED IN EACH BAGGED PATCH CORD.
 - SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	17897	3/21/12	UPDATED NOTE #1	CG	

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES: .XX = ±.01 (.25) .XXX = ±.005 (.127) .XXXX = ±.0025 (.0635) ANGLE TOL #1°

PROJECT REFERENCE: 2010-0222

MATERIAL: SEE NOTES

DRAWN BY: C. GRIBBLE 11/02/10

CHECKED BY:

APPROVED BY:

HUBBELL
Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE: HIGH DENSITY LC-LC DUPLEX PATCH CORDS MULTIMODE, 50/125, OM3

SIZE: C

DRAWING NO.: HWS13005C

SCALE: NTS

SHEET 1 OF 1

REV. 2