



CATALOG NUMBER	DESCRIPTION	FIBER TYPE	SPLIT SLEEVE MAT'L	ADAPT. BODY COLOR
OCLCD50	OPTICAL CASSETTE HD LC DUP/MTP	50/125um OM2 MULTIMODE	PHOSPHOR BRONZE	BLACK
OCLCD50G	OPTICAL CASSETTE HD LC DUP/MTP	50/125um OM3 MULTIMODE	PHOSPHOR BRONZE	AQUA
OCLCD50G4	OPTICAL CASSETTE HD LC DUP/MTP	50/125um OM4 MULTIMODE	PHOSPHOR BRONZE	AQUA
OCLCD62	OPTICAL CASSETTE HD LC DUP/MTP	62.5/125um OM1 MULTIMODE	PHOSPHOR BRONZE	BEIGE
OCLCD5M	OPTICAL CASSETTE HD LC DUP/MTP	9/125um OS2 SINGLEMODE	ZIRCONIA	BLUE



NOTES:

- SUPPLIED WITH PUSH/PULL FASTENERS FOR EASY INSTALLATION/REMOVAL.
- PANELS FIT INTO HUBBELL WALL MOUNT AND RACK MOUNT CABINETS.
- BLACK ELECTROSTATICALLY APPLIED POWDER COAT.
- ADAPTERS SUPPLIED WITH DUST CAPS INSTALLED.
- FULLY TESTED WITH TEST DATA INCLUDED.
- 50/125um OM3 MULTIMODE FIBER IS RATED FOR 10Gb/s TRANSMISSION FOR UP TO 300 METERS AT 850nm.
- 50/125um OM4 MULTIMODE FIBER IS RATED FOR 100Gb/s TRANSMISSION FOR UP TO 125 METERS AT 850nm.
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
2	19601	03/17/15	UPDATED MATERIAL CALLOUT	MMA	

Created on AUTOCAD	DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES .X = ±.03 (.8) .XX = ±.02 (.4) .XXX = ±.010 (.25) ANGLE TOL ±1°		PROJECT REFERENCE: <b>2012-003</b>		 <b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378
	IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION		MATERIAL: C.R.S.; ENGINEERING THERMOPLASTIC		
			DRAWN BY: C. GRIBBLE 2/22/12		TITLE: <b>24 PORT FIBER OPTICAL CASSETTE HIGH DENSITY LC DUPLEX/MTP</b>
			CHECKED BY:		SIZE: <b>C</b>
		APPROVED BY:		DRAWING NO.: <b>HWS14017C</b>	
				SCALE: <b>1/1</b>	
				SHEET <b>1</b> OF <b>1</b>	
				REV. <b>2</b>	