


CATALOG NUMBER	DESCRIPTION	FIBER TYPE	SPLIT SLEEVE MAT'L	ADAPT. BODY COLOR
OCLC050	OPTICAL CASSETTE LC QUAD/MP0	MULTIMODE 50/125	PHOS-BRONZE	BLACK
OCLC062	OPTICAL CASSETTE LC QUAD/MP0	MULTIMODE 62.5/125	PHOS-BRONZE	BEIGE
OCLC05M	OPTICAL CASSETTE LC QUAD/MP0	SINGLEMODE 9/125	ZIRCONIA	BLUE
OCLC050G	OPTICAL CASSETTE LC QUAD/MP0	50/125 OM3	PHOS-BRONZE	AQUA
OCLC050G4	OPTICAL CASSETTE LC QUAD/MP0	50/125 OM4	PHOS-BRONZE	AQUA



- NOTES (UNLESS OTHERWISE SPECIFIED):
1. SUPPLIED WITH PUSH/PULL FASTENERS FOR EASY INSTALLATION/REMOVAL.
 2. CASSETTES FIT INTO HUBBELL WALL MOUNT AND RACK MOUNT CABINETS.
 3. BLACK ELECTROSTATICALLY APPLIED POWDER COAT.
 4. ADAPTERS SUPPLIED WITH DUST CAPS INSTALLED.
 5. FULLY TESTED WITH TEST DATA INCLUDED. MAX INSERTION LOSS FOR ANY SINGLE CHANNEL IS 1.5dB.
 6. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
D	17867	2/22/12	ADDED OCLC050G4 CATALOG #	CG	

Created on AUTOCAD

DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES (MM).

TOLERANCES
.X = ±.03 (.8)
.XX = ±.02 (.4)
.XXX = ±.010 (.25)
ANGLE TOL. ±1°

PROJECT REFERENCE: 021-08

MATERIAL: .060" C.R.S ENGINEERING THERMOPLASTIC

DRAWN BY: C. DUSSAULT 6/2/08

CHECKED BY:

APPROVED BY:

HUBBELL
Hubbell Premise Wiring
HUBBELL INCORPORATED (Delaware)
14 Lord's Hill Road, Stonington, Connecticut 06378

TITLE: FIBER OPTICAL CASSETTE LC QUAD/MP0

SIZE: DRAWING NO. C HWS12683C

SCALE: 1/1 SHEET 1 OF 1