

NEMA NO.	RATING	POLE/WIRE	CAT. NO.	BLADE CONFIGURATION	VOLTAGE COLOR CODE
L5-20P	125V	2P/3W GROUNDING	HBL2311ST HBL2311STBK	(W) JG	YELLOW
L6-20P	250V	2P/3W GROUNDING	HBL2321ST HBL2321STBK	( ) Je	BLUE
L7-20P	277VAC	2P/3W GROUNDING	HBL2331ST	(W) JG	GRAY
L8-20P	480VAC	2P/3W GROUNDING	HBL2341ST	X JG	RED

## **NOTES (UNLESS OTHERWISE SPECIFIED):**

- 1. DIMENSIONS ARE IN INCHES [mm].
- 2. ALL DEVICES ARE cULus LISTED & FED SPEC.
- 3. CORD TYPES: S & SJ
- 4. CORD CLAMP RANGE: 0.35 [9 mm] 0.93 [24 mm].
- 5. WIRING TERMINAL ACCOMMODATION: 14 AWG 8 AWG STRANDED COPPER WIRE ONLY.
- 6. ASSEMBLY SCREWS ARE PHILLIPS/SLOTTED/ROBERTSON HEAD.
- 7. CATALOG NUMBERS & RATING ARE PAD PRINTED ON THE SIDE OF THE DEVICE, COLOR CODED BY VOLTAGE.

LIST OF PARTS					
DESCRIPTION	MATERIAL	FINISH	표텔		
COVER	NYLON	BLACK			
CORD CLAMP	NYLON	NATURAL,	31 S		
COND CLAIVIP	INTLOIN	BLACK	[[]]		
BLADE HOLDER	NYLON	NATURAL,	<del>,</del>		
BLADE HOLDER	INYLON	BLACK	DIMENSION SHEET FOR CAT. NO HBL2311ST, HBL232		
RETAINER	NYLON	BLACK	23 AT.		
BLADES	COPPER ALLOY		21 6		
SPRING	STAINLESS STEEL		TS		
PLUNGER	NYLON		<u> </u>		
ASSEMBLY	STEEL	ZINC PLATE	뽄		
FASTENERS	SIEEL	ZINCPLATE	23		
CORD CLAMP	NIVI ONI	DLACK	319		
INSERTS	NYLON	BLACK	,		
DUST SHIELD	TPE	BLACK	픎		
			123,		
			IMENSION SHEET FOR CAT. NO. HBL2311ST, HBL2321ST, HBL2331ST, HBL2341ST		



## CAT. NO. HBL2311ST (NOT SHOWN TO SCALE)

REV	DESCRIPTION	APP	DATE
	DCN 221011024714 AM		
	& BLADE HOLDER PER		
	BLACK FOR CORD CLAMP		
2	NATURAL WITH NATURAL,	MAM	12/09/22
	HBL2321STBK, REPLACED		
	HBL2311STBK &		
	ADDED CAT#		

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE

## 20A 3-WIRE TWIST-LOCK® EDGE SCREWLESS TERMINATION PLUG



WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT

CAGE CODE 74545

M-14324

2

 $\square$