


DR. NO. M-14636 SHEET 2 OF 3

1 REVISIONS	
SUB.	
1	9/12/23 INITIAL RELEASE PER DCN 240116036057 VMK TAB

ISO STANDARD FOR 3rd ANGLE PROJECTION	
"IN ACCEPTING OUR DRAWINGS OR BLUEPRINTS FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION OR DESIGNS THEREIN SHOWN, AND THAT YOU WILL MAKE NO USE OF OUR DRAWINGS OR BLUEPRINTS OR OF THE IDEAS, INFORMATION OR DESIGNS THEREIN SHOWN WITHOUT OUR PERMISSION."	
DO NOT SCALE DRAWING. USE DIMENSIONS ONLY. DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.	
MATERIAL	N/A
FINISH	N/A
TITLE	60/100A ASSEMBLY INSTRUCTIONS
HUBBELL WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
TOLERANCES UNLESS OTHERWISE SPECIFIED XX = ± .01 XXX = ± .005 X.XXX = ± .0005 ANGLE TOL. ±1°	DR. BY VMK CHK. BY TAB PROJECT NO.
SCALE 1:1.5 DATE 9/12/23	
DR. NO. M-14636	
SIZE D	SHEET 2 OF 3



REVISIONS	
SUB.	1
1	9/12/23 INITIAL RELEASE PER DCN 240116036057 VMK TAB

ISO STANDARD FOR 3rd ANGLE PROJECTION	
"IN ACCEPTING OUR DRAWINGS OR BLUEPRINTS FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION OR DESIGNS THEREIN SHOWN, AND THAT YOU WILL MAKE NO USE OF OUR DRAWINGS OR BLUEPRINTS OR OF THE IDEAS, INFORMATION OR DESIGNS THEREIN SHOWN WITHOUT OUR PERMISSION."	
DO NOT SCALE DRAWING. USE DIMENSIONS ONLY. DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED.	
MATERIAL	N/A
FINISH	N/A
TITLE	60/100A ASSEMBLY INSTRUCTIONS
HUBBELL WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
TOLERANCES UNLESS OTHERWISE SPECIFIED XX = ± .01 XXX = ± .005 ANGLE TOL. ± 1°	DR. BY VMK CHK. BY TAB SCALE 1:1.75 DATE 9/12/23 PROJECT NO.
DR. NO.	M-14636
SIZE D	SHEET 3 OF 3