



M-14695


1



20A/125V DEVICE SHOWN



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TOP COVER	PC (f1)	-
BASE	PC	-
BRIDGE	COPPER ALLOY	-
GROUND CONTACTS	COPPER ALLOY	-
LINE CONTACTS	COPPER ALLOY	-
REAR COVER	PC	-
PLUNGER	NYLON	-
SPRING	STAINLESS STEEL	-
STAPLE	STAINLESS STEEL	-
WASHER	PVC FILM	BLACK
GROUND STRAP	COPPER ALLOY	-
MOUNTING SCREW	STAINLESS STEEL	PASSIVATE



CATALOG NO: HBL5262STWR
NOT SHOWN TO SCALE

CATALOG NO: HBL5362STWR
NOT SHOWN TO SCALE

HUBBELL CATALOG NUMBERS					
AMPERAGE	BLACK	BLUE	BROWN	GRAY	IVORY
15A	HBL5262STBKWR	HBL5262STBLWR	HBL5262STWR	HBL5262STGYWR	HBL5262STIWR
20A	HBL5362STBKWR	HBL5362STBLWR	HBL5362STWR	HBL5362STGYWR	HBL5362STIWR
	LT. ALMOND	RED	WHITE	GREEN	ORANGE
15A	HBL5262STLAWR	HBL5262STRWR	HBL5262STWWR	HBL5262STGNWR	HBL5262STOWR
20A	HBL5362STLAWR	HBL5362STRWR	HBL5362STWWR	HBL5362STGNWR	HBL5362STOWR

GENERAL NOTES:

- 1. DIMENSIONS ARE IN INCHES [MM].
- 2. ALL DEVICES UL LISTED, CSA & FED. SPEC. CERTIFIED
- 3. TERMINALS ACCOMMODATE #14 - #10 AWG COPPER WIRE ONLY.

1	INITIAL RELEASE PER DCN 231120034858 WHD DSL	WHD	11/17/23
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].			
TITLE INDUSTRIAL WR DUPLEX RECEPTACLE, EdgeConnect, 15A & 20A, FED SPEC			
 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = $\pm$.01 .XXX = $\pm$.005 ANGLE TOL. $\pm$ 2°	DR. BY WHD	SCALE 1 : 1	
	CHK. BY DSL	DATE 11/13/23	