




M-14698

1



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
TOP COVER	PC (f1)	-
BASE	PC	-
BRIDGE	.04 GALV. STL.	-
GROUND CONTACTS	COPPER ALLOY	-
LINE CONTACTS	COPPER ALLOY	-
REAR COVER	PC	-
PLUNGER	NYLON	-
SPRING	STAINLESS STEEL	-
STAPLE	STAINLESS STEEL	-
WASHER	PVC FILM	BLACK
GROUND STRAP	COPPER ALLOY	-
MOUNTING SCREW	STAINLESS STEEL	PASSIVATE



HUBBELL CATALOG NUMBERS					
AMPERAGE	BLACK	BLUE	BROWN	GRAY	IVORY
15A	BR15STBKWTR	BR15STBLWRTR	BR15STWRTR	BR15STGYWRTR	BR15STIWRTR
20A	BR20STBKWTR	BR20STBLWRTR	BR20STWRTR	BR20STGYWRTR	BR20STIWRTR
	LT. ALMOND	RED	WHITE	GREEN	ORANGE
15A	BR15STLAWTR	BR15STRWRTR	BR15STWWTR	BR15STGNWRTR	BR15STOWTR
20A	BR20STLAWTR	BR20STRWRTR	BR20STWWTR	BR20STGNWRTR	BR20STOWTR

GENERAL NOTES:

- DIMENSIONS ARE IN INCHES [MM].
- ALL DEVICES UL LISTED, CSA & FED. SPEC. CERTIFIED
- TERMINALS ACCOMMODATE #14 - #10 AWG COPPER WIRE ONLY.

CAGE CODE 74545

CATALOG NO: BR15STWRTR NOT SHOWN TO SCALE			
CATALOG NO: BR20STWRTR NOT SHOWN TO SCALE			
1	INITIAL RELEASE PER DCN 231120034858 WHD DSL	WHD	11/17/23
REV	DESCRIPTION	APP	DATE
THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].			
TITLE WR DUPLEX RECEPTACLE, EdgeConnect, 15A & 20A TR, COMMERCIAL			
 WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT			
TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°		DR. BY WHD CHK. BY DSL	SCALE 1 : 1 DATE 11/13/23

DIMENSION SHEET FOR CAT. NO.
SEE TABLE

B

M-14698

1