




M-14735

1



FOR TOP FEED CONDUIT HUB
(ALL OTHER NOTES ARE THE SAME AS
CAT#. HBLDS60PJ/ HBLDS100PJ)




CATALOG NO. HBLDS60TPJ/ HBLDS100TPJ
(NOT SHOWN TO SCALE)

2X 1-1/4" NPT CONDUIT FITTING
SUPPLIED, PROVISION FOR
TOP, BOTTOM, & BACK FEED CUSTOMER
TO DRILL OR PUNCH
1-3/4" DIA. HOLE FOR CONDUIT FITTING

NOTES UNLESS OTHERWISE SPECIFIED:

1. DIMENSIONS SHOWN ARE IN INCHES.
2. ENCLOSURE TYPE 4X, 12.
3. cULus LISTED.
4. NSF CERTIFIED AND IP69K RATING.




CATALOG NO.'S	
HBLDS60PJ	
60 AMP	600 VAC
7.5 HP (5.6 kw)	120 VAC 1 ϕ
15 HP (11.19 kw)	200-240 VAC 1 ϕ
30 HP (22.37 kw)	480 VAC 1 ϕ
30 HP (22.37 kw)	200-240 VAC 3 ϕ
50 HP (37.28 kw)	480 VAC 3 ϕ
50 HP (37.28 kw)	600 VAC 3 ϕ

CATALOG NO.'S	
HBLDS100PJ	
100 AMP	600 VAC
7.5 HP (5.6 kw)	120 VAC 1 ϕ
15 HP (11.19 kw)	200-240 VAC 1 ϕ
30 HP (22.37 kw)	480 VAC 1 ϕ
30 HP (22.37 kw)	200-240 VAC 3 ϕ
50 HP (37.28 kw)	480 VAC 3 ϕ
50 HP (37.28 kw)	600 VAC 3 ϕ

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
ALL EXTERNAL PLASTIC PARTS	UV STABILIZED POLYESTER BLEND	
ALL EXTERNAL SCREWS	STAINLESS STEEL	
THREADED HUB	DIE CAST	
INSULATED THROAT	ZINC	
JOG SW.	PLASTIC	
GREEN LEDS		



CATALOG NO. HBLDS60PJ/ HBLDS100PJ
(NOT SHOWN TO SCALE)

1	INITIAL RELEASE PER DCN 240116036057	TAB	10/25/23
REV	DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE
PRODUCT SHOWN ON THIS DRAWING ARE
SUBJECT TO CHANGE WITHOUT NOTICE.
DIMENSIONS ARE IN INCHES [mm].

TITLE
DIMENSION SHEET FOR
60A & 100A CIRCUIT LOCK™
DISCONNECT SWITCHES



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS
OTHERWISE SPECIFIED
.XX = ± .01
.XXX = ± .005
ANGLE TOL. ±2°

DR. BY VMK
CHK. BY TAB

SCALE 1:3
DATE 10/9/23