

NOTES:


1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS].
2. PRODUCT IS cULus LISTED.
3. MOUNTING HARDWARE INCLUDED.

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
FACE PLATE	CRS	PRE-GALVANIZED
PARTITION	CRS	PRE-GALVANIZED

REV	DESCRIPTION	APP	DATE
3	REVISED PER EC 221108025468	KG	11/9/2022
2	REDRAWN & REVISED PER DCN 23447	SBW	2/5/18

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE MOUNTING PLATE, NEMA INTERMEDIARY, RECESSED 10 GANG FLOOR BOX



TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2'	DR. BY SBW	SCALE 1/2
	CHK. BY	DATE 2/2/18