



- NOTES: (UNLESS OTHERWISE SPECIFIED)
1. INTERPRET THIS DRAWING IN ACCORDANCE WITH ASME Y14.5-2009 STANDARD.
 2. INDICATES CRITICAL FUNCTION OR PROCESS REQUIREMENT.
 3. DIMENSIONS ARE SYMMETRICAL ABOUT THE CENTERLINE TO WITHIN HALF OF THE OVERALL TOLERANCES.
 4. CLEAN SURFACE WITH ISOPROPYL ALCOHOL PRIOR TO MARKING.

CAGE CODE 74545

M-14767

1

PAD PRINTING PARAMETERS:

MACHINE: TRANS-TECH MODEL SEAL CUP 60

COLOR: BLACK (130201)

FORMULATION:

FOR 15g OF PAINT:

- i. PAINT TYPE B- 15.0g
- ii. HARDENER LMN 120303- 3.75g
- iii. THINNER VD- 1.9g

TOTAL GRAMS: 20.65g

FOR 20g OF PAINT:

- i. PAINT TYPE B- 20.0g
- ii. HARDENER LMN 120303- 5.0g
- iii. THINNER VD- 2.5g

TOTAL GRAMS: 27.5g

SKU	COLOR	WR
GFRT20C2W	WHITE	NO
GFRT20C2I	IVORY	NO
GFRTW20C2W	WHITE	YES
GFRTW20C2I	IVORY	YES

LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
FACE	NYLON 66	-
BASE	NYLON 66	-
BRIDGE	STEEL	GALVANIZED
CONTACTS	BRASS	-
MOUNTING SCREWS	STEEL	-
MOUNTING SCREWS (WR ONLY)	STAINLESS STEEL	-
TERMINALS	BRASS	TIN

1	INITIAL RELEASE PER ECN 240307037531	JR	3/14/2024
---	---	----	-----------

REV	DESCRIPTION	APP	DATE
-----	-------------	-----	------

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE
MRKD CNTRLD GFCI 20A PAD PRINT LAYOUT

WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLE TOL. ±2°	DR. BY JR CHK. BY	SCALE 2 : 1 DATE 3/14/2024
---	----------------------	-------------------------------