


CAT NO.	NEMA NO.	RATING	POLE/WIRE	CONFIGURATION	RATING RING COLOR
HBL2410ST	L14-20	20A 125/250V	3P/4W GROUNDING	G W	ORANGE
HBL2420ST	L15-20	20A 250V 3Ø	3P/4W GROUNDING	G Y Y	BLUE
HBL2430ST	L16-20	20A 480V 3Ø	3P/4W GROUNDING	G Y Y	RED

NOTES:

- 1. DIMENSIONS ARE IN INCHES [mm].
- 2. WIRING TERMINAL ACCOMMODATION:
 - a. SOLID WIRE: 14 AWG 10 AWG COPPER WIRE ONLY
 - b. STRANDED WIRE (INCLUDING COMPACT STRANDED): 14 AWG 8 AWG COPPER WIRE ONLY
- 3. CONDUCTOR STRIP LENGTH: 0.600" (15.24mm)

LIST OF PARTS					
DESCRIPTION	MATERIAL	FINISH			
COVER	THERMOPLASTIC				
MID HOUSING	THERMOPLASTIC				
BASE	THERMOPLASTIC				
CONTACTS	BRASS				
SPRING	STEEL				
PLUNGER	THERMOPLASTIC				
GR. SHUNT	BRASS				
MOUNTING	BRASS				
PLATE	DNASS				
RIVET	BRASS				
		_			



	DESCRIPTION	ΔPP	
RFV			DATE
1	190604142428 RGP	ILS	05/17/19
	INITIAL RELEASE PER DCN	TLS	
- 1	DCN 220315017977 AM		
	UPDATED IN NOTES PER	RGP	03/14/22
	CONDUCTOR RANGE		

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE IN INCHES [mm].

TITLE

CUST. DWG, 20A 4 WIRE SPRING TERMINATION RECEPTACLE



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED $.XX = \pm .01$ $.XXS = \pm .005$ ANGLE TOL. $\pm 2^{\circ}$ CHK. BY TLS DATE 05/17/19

CAGE CODE 74545

M-14074

W