


M-7241 5



CAT. NO	*FITS PLUGS & INLETS	DIM. "A"	∅ "B"	LENGTH "C"
PC320	ALL 16 & 20A 3 WIRE	1.62	2.09	24 ±2"
PC420	ALL 16 & 20A 4 WIRE	1.62	2.37	24 ±2"
PC520	ALL 16 & 20A 5 WIRE	1.62	2.68	24 ±2"
PC3430	ALL 30 & 32A 3 & 4 WIRE	2.01	2.85	24 ±2"
PC530	ALL 30 & 32A 5 WIRE	2.01	3.12	24 ±2"
PC60	ALL 60 & 63A	2.84	3.33	24 ±2"
PC100	ALL 100 & 125A	3.12	3.86	24 ±2"
PC343OCT	ALL 30 & 32A 3 & 4 WIRE	2.01	2.85	11 ±1"

CATALOG NO. INCLUDES THE FOLLOWING

- CLOSURE CAP
- LANYARD ASSEMBLY (UNATTACHED: PACKED IN ENVELOPE) CONSISTS OF:
 - "C" NYLON LANYARD WITH LOOP AT ONE END.
 - CABLE CLAMP
- INSTRUCTION SHEET

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
CLOSURE CAP	PBTB/PC BLEND	GRAY
CABLE CLAMP	NYLON	BLACK
LANYARD	NYLON	WHITE

SYM	REVISIONS	APP	DATE
5	ADDED PC343OCT AND "C" DIM TO TABLE. CORD VIEW "NYLON LANYARD WAS 24" NYLON LANYARD & LENGTH "C" WAS 24 ±2". PER DCN 19065. MYA	PJB	8/31/12
4	REMOVED ALL REFERENCE TO WASHER AND VIEW OF COILED LANYARD. ADDED UNCOILED VIEW OF THE LANYARD AND 24" DIM. PER DCN18511 TCM	DJP	12/20/11
3	ADDED TOLERANCE TO DIMS. "A" & "B" PER DCN 18364 RCM	DJP	10/3/11
2	NYLON LANYARD, KNOT WAS CRIMP SLEEVE. "LIST OF PARTS" TABLE: REMOVED CHRIMP SLEEVE PER DCN 11709 SPN	JPP	5/19/04
1	"X" REMOVED; LAST "X" REVISION WAS "X-0" PER DCN #2565 JMN	ZIMM	2/15/94

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE
CLOSURE CAP ASSEMBLY, PIN & SLEEVE

TOLERANCES UNLESS OTHERWISE SPECIFIED .XX = ± .01 .XXX = ± .005 ANGLES = ± 2°	WIRING DEVICE-KELLEMS HUBBELL INCORPORATED SHELTON, CT	
	DR. BY JMN	APP. BY ZIMM
	TR. BY	SCALE NONE
CHK. BY	DATE 2/15/94	

DIMENSION SHEET FOR CAT. NO. M-7241
 REPAIRABLE NON-REPAIRABLE B