


CORD CLAMP INSERT ROTATED 180° & ¬
ALIGNED WITH THIS LINE FOR:
CORDType SV: 16/3
CORD Type SJ: 16/3
Cord Diameter: 0.23 to 0.35 inch
(5.8 to 8.9 mm)


REMOVE CORD CLAMP INSERT FOR: CORD Type S: 14/3 - 10/3

CORD Type SJ: 10/3 Cord Diameter: 0.48 to 0.72 inch (12 to 18.3 mm)

Cord Diameter: 0.40 to 0.72 mem (12 to 13.5 mm)

Ø1.527±.015
[38.79±0.38]





CORD CLAMP INSERT SHIPPED FROM FACTORY AS SHOWN AND ALIGNED WITH THIS LINE FOR:

CORD: Type S: 16/3 Type SJ: 14/3 - 12/3

HBL5266CBKST,

HBL52CM66CST,

HBL8215CST, HBL8215CTST HBL5366CST, HBL5366CBKST,

HBL53CM66CST,

HBL8315CST.

HBL8315CTST

HBL5666CST,

HBL56CM66CST

HBL5466CST,

HBL54CM66CST

Cord Diameter: 0.36 to 0.47 inch (9 to 11.9 mm)

2P/3W

**GROUNDING** 

2P/3W

**GROUNDING** 

2P/3W

**GROUNDING** 

2P/3W

**GROUNDING** 

— CAT. NO. & RATING PRINTED ON CORD CLAMP

Δ	RATING	POLE/WIRE	CAT. NO.	BLADE CONFIGURATION	
			HBL5266CST,	G	CAT. NO. HBL5366CST

w []

W

\_ \_

**9** 


## **NOTES (UNLESS OTHERWISE SPECIFIED):**

- 1. DIMENSIONS ARE IN INCHES [mm].
- 2. ALL DEVICES ARE cULus LISTED.
- 3. WIRING TERMINAL ACCOMMODATION: 16 AWG 10 AWG STRANDED COPPER WIRE ONLY.
- 4. ASSEMBLY SCREWS ARE PHILLIPS/SLOTTED.
- 5. CORD CLAMP SCREWS ARE PHILLIPS/SLOTTED/ROBERTSON HEAD.
- 6. CATALOG NUMBERS ARE PAD PRINTED ON THE CORD CLAMPS.
- 7. ON "CM" DEVICES, STEEL PARTS ARE MADE OF STAINLESS STEEL AND ALL COPPER ALLOY PARTS ARE NICKEL PLATED.
- 8. ON "BK" DEVICES, ALL EXTERIOR NYLON PARTS ARE BLACK.
- 9. THE FOLLOWING CATALOG NUMBERS ARE HOSPITAL GRADE & MEET THE PERFORMANCE REQUIREMENTS OF FED. SPEC. W-C-596G/GEN: HBL8215CST, HBL8315CTST, HBL8315CTST, HBL8215CTST

WITHOUT BACK COVER ASSEMBLY

**SCALE 1:1** 

LIST OF PARTS							
DESCRIPTION	MATERIAL	FINISH					
BLADE HOLDER	NYLON	NATURAL					
RETAINER	POLYCARBONATE	CLEAR					
COVER	NYLON	BLACK					
CORD CLAMP	NYLON	NATURAL					
COVER	POLYCARBONATE	CLEAR					
(TRANSPARENT)	POLICANDONATE	CLEAN					
CORD CLAMP	NIVLONI	BLACK					
INSERT	NYLON						
CONTACT BLADE	COPPER ALLOY						
GROUND BLADE	COPPER ALLOY						
SPRING	STAINLESS STEEL						
PLUNGERS	NYLON						
DRIVE SCREW	STEEL	ZINC PLATE					
ASSY. SCREWS	STEEL	ZINC PLATE					
CORD CLAMP SCREWS	STEEL	ZINC PLATE					



				_	
1	INITIAL RELEASE PER DCN	MAM	1/4/24		
Т	230906033177				
REV	DESCRIPTION	APP	DATE		

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE.
DIMENSIONS ARE IN INCHES [mm].

TITLE

2-POLE 3-WIRE STRAIGHT BLADE EDGE SCREWLESS TERMINATION PLUG



WIRING DEVICE-KELLEMS
HUBBELL INCORPORATED
SHELTON, CT

TOLERANCES UNLESS OTHERWISE SPECIFIED  $XX = \pm .01$   $XX = \pm .005$  ANGLE TOL.  $\pm 2$  DR. BY RR SCALE 1:1 DATE 1/4/24

CAGE CODE 74545

NEMA NO.

5-15P

5-20P

6-15P

6-20P

15A 125V

20A 125V

15A 250V

20A 250V

M-14563

DIMENSION SHEET FOR CAT. NO.
SEE TABLE

000