



CATALOG NUMBER	DESCRIPTION
PR10720	17" HORIZONTAL/VERTICAL POWERSTRIP

SPECIFICATIONS:	
MADE IN USA	YES
AC RATING VOLTS	125 OR 250
AC RATING AMPS	20 de-rated to 16
AC RATING WATTS	2000 or 4000 - per circuit
AC RATING FREQUENCY	50/60 Hz
OVER CURRENT PROTECTION	NONE
POWER SWITCH	NO
PLUG TYPE	IEC320 C-20 POWER INLET W/ CORD RETAINING CLAMP
RECEPTACLE TYPE	IEC320 C-13
RECEPTACLES STYLE	GROUPED
RECEPTACLES ON FACE	10
MAXIMUM OUTPUT PER RECEPTACLE	15A @ 125V OR 15A @ 250V PER RECEPTACLE BANK
CERTIFICATION/AGENCY APPROVALS	UL & c-UL LISTED ACCESSORY 60950
UNIT WEIGHT	2.4 lbs.



## NOTES:

- KIT SHOULD CONTAIN:
  - POWER STRIP PER TABULATED SPECIFICATIONS.
  - SMALL "L" BRACKET
  - 10-32 X 1/2 PANHEAD PHILLIPS SCREW W/ INTEGRAL STAR WASHER.
  - HARDWARE PACK - MOUNTING SCREWS, BAGGED W/ WASHERS
  - INSTALLATION INSTRUCTIONS
- SURFACE FINISH: BLACK
- SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE



REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
A	5390	8/5/04	INITIAL RELEASE	GPE	NJH

Created on AUTOCAD		DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES X = ±.03 (.8) .XX = ±.02 (.4) .XXX = ±.010 (.25) ANGLE TOL ±1°	
PROJECT REFERENCE: <b>2004-112</b>		DRAWN BY: GLEN P. EIGO, 8/5/04	
MATERIAL: HEAVY STEEL		CHECKED BY: DAVE MCBAIN, 8/16/04	
APPROVED BY: NATE HERRING, 8/16/04		TITLE: <b>17" VERTICAL/HORIZONTAL POWER STRIP, BLACK            NON-SURGE PROTECTED - 10 OUTLETS</b> 16A, 125/250 VAC	
HUBBELL <b>Hubbell Premise Wiring</b> HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Storington, Connecticut 06378		SIZE DRAWING NO. <b>C12013</b>	
SCALE: NTS		SHEET 1 OF 1	
REV.		<b>A</b>	