



- NOTES:**
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
  2. BOX VOLUME: 15.5 IN<sup>3</sup> [254.0 CM<sup>3</sup>]
  3. ACCEPTS CEILING FIXTURES UP TO 50LBS [22.67 KG].
  4. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2" KO	A,B,C	1

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BOX	STEEL	GALVANIZED
MOUNTING SCREW	STEEL	GALVANIZED
J BRACKET	STEEL	GALVANIZED
X CLAMP	STEEL	GALVANIZED
CLAMP SCREW	STEEL	GALVANIZED

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	N.S.	02/26/2016

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:  
**4" OCTAGON BOX 1-1/2" DEEP WITH X CLAMPS & J BRACKET**

TOLERANCE UNLESS OTHERWISE SPECIFIED  
 .XX DECIMAL ±.015  
 .XXX DECIMAL ±.005  
 ANGLE ±2°

**RACO**  
 South Bend, Indiana

DRAWN BY:	J.R.	SCALE:	1:2.5
APP. BY:	N.S.		
DATE:	02/26/2016		

157 CUS

157 DIMENSION SHEET FOR CAT. NO.

SIZE: **A**