




CONTROL TERMINALS WILL ACCEPT #6 THRU #14 AWG WIRE
LINE/LOAD TERMINALS WILL ACCEPT #4 THRU #1/0 AWG WIRE



CAST ALUMINUM WEATHERPROOF CASE WITH BRACKET




FUSE - DUAL ELEMENT, CLASS RK5 - 600V/100A





NAMEPLATE DETAIL

CONNECTIONS FOR TYPE MR-DNX 2P RELAY
RATED 100A 277/480V 60HZ WITH PHOTO CONTROL UNIT



1. PHYSICAL LOCATION OF LINE 1 & 2 AND LOAD 1 & 2 REVERSED.
2. ACTUAL WIRES TO AUTO AND HAND SIDES OF SWITCH REVERSED DUE TO SWITCH DESIGN.
3. FOR STREET LIGHTING APPLICATIONS THE CONTINUOUS LOAD SHOULD NOT EXCEED 80% OF THE FUSE RATING. LOAD CONNECTION IS LINE TO NEUTRAL.

THIS DRAWING AND ALL INFORMATION THEREON IS THE SOLE PROPERTY OF TRINETICS. IT MUST NOT BE COPIED, REPRODUCED OR SUBMITTED TO OTHERS WITHOUT WRITTEN AUTHORIZATION. ALL REPRODUCTIONS ARE SUBJECT TO RETURN ON DEMAND.				
		RELAY ASSEMBLY MR-DNX SPEC 6863		
	THIRD ANGLE PROJECTION	SIZE B	DRAWN BY M Matuszewski	DATE 12/10/11
ALL DIMENSIONS ARE IN INCHES UNLESS OTHERWISE SPECIFIED		FAMILY ID C1643	APPROX. WEIGHT 24 LB	SCALE 5/16
PART NUMBER 33188400				