


PIGTAIL:
 WIRE: #12 AWG STRANDED, 10-1/2" LONG, GREEN
 INSULATED, U.L. LISTED, 600 VOLT MAX;
 EXTRA-GRIP RING TERMINAL, 16/12 AWG BRASS;
 #10-32 X 3/8" GROUND SCREW W/COMBO HEX WASHER
 HEAD (SLOTTED, #2 PHILLIPS AND ROBERTSON)

REVISIONS			
REV.	DATE	DESCRIPTION	BY
-	03-05-24	INITIAL RELEASE	RMV

FILE NO.: 189HS CUS



DESCRIPTION	MATERIAL	FINISH
PIG TAIL	COPPER	SEE DRAWING
FAR SIDE SUPPORT	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
SPACER	STEEL	GALVANIZED

LIST OF PARTS

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:

4" SQ BOX W/ FAR SIDE SUPPORT, STUD BRACKET, & GROUND

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO*	A, B, C, D	1
(1/2"-3/4") TKO*	E	2
1/2" KO	A, B, C, D, E	2

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ± .015
 .XXX DECIMAL ± .005
 ANGLE ± 2°



DRAWN BY:	RMV	SCALE:	SIZE:
APP. BY:	N.S.		
DATE:	03-05-24	1:3	A

- NOTES:
 1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 21.0 IN³ [344.1 CM³]
 3. UL LISTED

DIMENSION SHEET FOR CAT. NO. 189HS

8.5in*1in