


D= H5 @

Y WOKAFGAY OAVUCPOOOFEBASUP OZOUOPÁ
 QUMSVOOAVESQUNVOOÁ €€XUSVÁ OYL
 OYVUCOEUQAUPOAVOUT QCSÉFI FGAY OAUOEUŁ
 AFEBHAYAD AKOUUMPOAUOUYAY EOUT OUPROYA OUPÓÁ
 POOQASUVVOOÁGAPGSSQUAOP OAUOOUVUUPD

F9J-G-CBG			
F9J"	85H9	89G7F-DHCB	6M
Ē	€ Ē Ē	QVQASU OŠOCEUOAU OAUOY QO	UT X

: BC " " GHUT JOMU



UO OVS	QUMSVOOÁ UVUCPOOÁ OUUOOU	PBE
QAVVOPOUU	UVOŠ	OCSXOPQOŠ
UO O	UVOŠ	OCSXOPQOŠ
UO OOU	UVOŠ	OCSXOPQOŠ
89G7F-DHCB	A5H9F-5 @	: -B-G<

8A 98GCB G-9H C F 7 5H " BC " 8 8GA

@GH'C: 'D5 FHG

H<989G> B'5B8 8-A 9BGC BGC; H<9DFC 8I 7 H
 G<CK B'CB H<68F5K -B; '5F9G 6>97 HHC
 7 <5B; 9K H<CI HBC H 9

HH<9.
**5 GG9 A 6 @M(" "GE' I ' & ! % # " " 8 9 9 D'
 6 CL' K H< ; FCI B 8 ' K F 9**

- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 30.3 IN³ [496.5 CM³]
 3. cULus LISTED

? BC ? CI HG		
VUO OAUZO	ŠU OCE/WP	UVYĚ
FBH D A V SU	OZ O O O O	F
FBASU	OZ O O O O	G
FBH D A V SU	O	G

HC @F5B7 9I B @GG C H< 9F K @9 GD97 ± 98		8F5K B'6M	UT X	G7 5 @.	G-N9.
"LL' 897 A 5 @+ "\$%) "LLL' 897 A 5 @+ "\$\$) 5 B: @ ± & "		5DD" 6M	PĚJE		
		85H9.	€ Ē Ē Ē	FKI	

100%