


LIST OF PARTS

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
BRACKETS	STEEL	GALVANIZED



- NOTES:**
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 30.3 IN³ [496.5 CM³]
 3. UL LISTED

SYMBOL	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	RMV	01/12/17

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE: **4" SQ. 2-1/8" DEEP WELDED BOX W/ FM LONG BRACKET**

RACO
South Bend, Indiana

DRAWN BY: RMV
APP. BY: N.S.
DATE: 01/12/17

SCALE: 1:2

KNOCKOUTS

TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	A.B.C.D	1
(1/2"-3/4") TKO®	E	2
1/2" KO	A.B.C.D	2
1/2" KO	E	3

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ±.015
.XXX DECIMAL ±.005
ANGLE ±2°