



CATALOG NUMBER	DESCRIPTION
MCCPSS19TS	ASSY, 19" 8 OUT 15AMP POWER STRIP



NOTES:

- PARAMETER SPECIFICATIONS
 OUTPUT RATING: 120VAC, 15 AMPS, 1800 WATTS 50/60HZ

 RECEPTACLES: 8 - NEMA 5-15R SINGLE
 FEATURES:
 - 8 OUTLETS - 4 FRONT 4 REAR
 - 15' 14/3 SJT POWER CORD
 - RESET SWITCH
 - POWER ON (GREEN) LED
- KIT SHOULD CONTAIN:
 (1) POWER STRIP PER ABOVE SPECIFICATIONS.
 (1) 77887001 HARDWARE KIT.
- SURFACE FINISH: DUPONT "BLACK WRINKLE" GFB 800 W3 OR MARTIN "MIDNIGHT BLACK WRINKLE" 12-7001

REV.	ECN	DATE	DESCRIPTION	CHD BY	APPD BY
A	3986	10/30/01	INITIAL RELEASE	PSM	

Dimensioning and tolerance per ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM).
 TOLERANCES
 .XX = ±.01 (.25)
 XXX = ±.003 (.127)
 XXXX = ±.0025 (.0635)
 ANGLE TOL. ±1°

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION.

PROJECT REFERENCE: PMS 512
 MATERIAL:
 DRAWN BY: PAUL S. MAGLIRE 10/30/01
 CHECKED BY:
 APPROVED BY:

HUBBELL Hubbell Premise Wiring
 HUBBELL INCORPORATED (Delaware)
 14 Lerch Hill Road, Shelton, Connecticut 06484

TITLE: ASSY, 19" RACK POWER STRIP
 8 OUT 15 AMPS, 120VAC, 50/60HZ

SIZE: D DRAWING NO. C10745 REV. A

SCALE: N/A SHEET 1 OF 1