



NOTES UNLESS OTHERWISE SPECIFIED:
 1. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.

DIMENSIONING AND TOLERANCING PER ANSI Y14.5M-1982, UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES
 .XX = ±.01 []
 .XXX = ±.005 []
 .XXXX = ±.0025 []
 ANGLE TOL ±1°

Created on V-13 UNIGRAPHICS

IN ACCEPTING OUR DRAWINGS, BLUEPRINTS, OR SUPPORTING DOCUMENTATION FOR QUOTATION OR OTHER PURPOSES, YOU AGREE NOT TO DISCLOSE TO OTHERS THE IDEAS, INFORMATION, OR DESIGNS SHOWN HEREIN, AND THAT YOU WILL MAKE NO USE OF SAME WITHOUT PERMISSION.

COMPONENTS CONTAINED IN THIS DOCUMENT MUST ADHERE TO ENVIRONMENTAL SPEC. HWS12367

PROJECT REFERENCE: 2014-003	Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 23 Clara Drive Suite 103, Mystic, Connecticut 06355
MATERIAL:	
DRAWN BY: D. PECK 6/9/15	TITLE: 2U TELESCOPING SERVER BRACKET
CHECKED BY:	SIZE: C DRAWING NO. HWS14519C
APPROVED BY:	REV. A

SCALE: NTS SHEET 1 of 1

REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY
A	19654	6/9/15	INITIAL RELEASE	DMP	