



8	7	6	5	4	3	2	1				
CATALOG NO.	CONDUCTOR CODE	BOLT SIZE	B	C	E	K	L	N	OD	T (REF)	Y MIN.
HGBL250DB	(AWG) 250Kcmil	3/8 [M10]	1.62 [41]	1.10 [26]	1.00[25]	.40 [10]	3.99 [101]	.41 [10]	.75 [19]	.14 [4]	1.43 [36]



- NOTES:
1. MATERIAL: COPPER TUBING.
 2. FINISH: TIN PLATED
 3. INSTALLATION TOOLING:
MECHANICAL DIE: HW29VT
HYDRAULIC DIE: HU29RT
WIRE STRIP LENGTH: 1-11/16
 4. SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.



1	18075	01/25/13	INITIAL RELEASE	MMA	
REV.	ECN	DATE	DESCRIPTION	CHG BY	APPD BY

Created on AUTOCAD		DIMENSIONING AND TOLERANCE PER ANSI Y14.5M-1982 UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES (MM). TOLERANCES XX = ±.01 (.25) XXX = ±.005 (.125) .XXX = ±.002 (.050) ANGLE TO .1°	
PROJECT REFERENCE: 2011-041		DRAWN BY: M. ABBY 01/23/13	
MATERIAL: SEE NOTES		CHECKED BY:	
		APPROVED BY:	
Hubbell Premise Wiring HUBBELL INCORPORATED (Delaware) 14 Lord's Hill Road, Stonington, Connecticut 06378		TITLE: 250Kcmil COPPER COMPRESSION LUG DOUBLE HOLE, 0.250" HOLE SIZE	
SIZE D	DRAWING NO. HWS777147C	SCALE: 1/1	REV. 1