



U.L. LISTED 600 VOLT MINIMUM.  
NO. 12 AWG GREEN TW INSULATED SOLID  
COPPER WIRE CUT 8-1/2" LONG IN FLAT,  
STRIPPED 1" IN FROM END.

- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
  2. BOX VOLUME: 18.0 IN<sup>3</sup> [295 CM<sup>3</sup>]
  3. 1 #12AWG SOLID COPPER WIRE 8" LONG PIG TAIL WITH GROUNDING SCREW INCLUDED
  4. UL LISTED

KNOCKOUTS	
TRADE SIZE	LOCATION
1/2" KO	1- ON THE BOTTOM (ACCESSIBLE AFTER REMOVAL STAB-IT CLAMP)
	2- ON EACH SIDE( 1 ACCESSIBLE ONLY AFTER REMOVAL STAB-IT CLAMP)
CABLE PRIOUTS	2- ON EACH SIDE OF THE SPACER

CABLE TYPES AND RANGES FOR STAB-IT CLAMP	
CABLE TYPES	CABLE RANGES
AC STEEL & ALUMINIUM	14-2,14-3,14-4,12-2,12-3,12-4,10-2,10-3
HCF AC STEEL	14-2,14-3,14-4,12-2,12-3,10-2,10-3
HCF AC ALMINUM	12-2,12-3,12-4,10-2,10-3
MC STEEL & ALUMINIUM	14-2,14-3,14-4,12-2,12-3,12-4,10-2,10-3
MCI-A STEEL & ALUMINIUM	14-2,14-3,14-4,12-2,12-3,12-4,10-2,10-3
HCF MCI-A STEEL	12-2,12-3,10-2
HCF MCI-A ALUMINIUM	14-2,14-3,14-4,12-2,12-3,12-4,10-2,10-3
3/8 TRADE SIZE FLEX,REFMC CONDUIT STEEL & ALUMINIUM. ANTI SHORT BUSHING REQUIRED	
CABLE RANGE .400" DIA. MIN TO .605" DIA. MAX	

**LIST OF PARTS**

DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDES	STEEL	GALVANIZED
PLASTER EARS	STEEL	GALVANIZED
STUD BRACKET	STEEL	GALVANIZED
FASTENERS	STEEL	GALVANIZED
STAB-IT™ CLAMP	STEEL	GALVANIZED
PIG TAIL	COPPER	

SYMBOL	INITIAL RELEASE	K.K.	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:  
**3-1/2" " DEEP GANGABLE SWITCH BOX WITH TS STUD BRACKET & STAB-IT® BX/MC CABLE CLAMP**

TOLERANCE UNLESS OTHERWISE SPECIFIED		<p><b>RACO</b> South Bend, Indiana</p>	SCALE: <b>1:2</b>
.XX DECIMAL ±.015	DRAWN BY: <b>K.K.</b>		
.XXX DECIMAL ±.005	APP. BY: <b>N.S.</b>		
ANGLE ±2°	DATE: <b>10/07/2016</b>		