



NOTES:

1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
2. BOX VOLUME: 15.5 IN³ [254.0 CM³]
3. ACCEPTS CEILING FIXTURES UP TO 50 LBS. [22.67 KG]
4. UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2" KO	A	4
1/2" KO	B, C, D, E	1

LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
BOX	STEEL	GALVANIZED
SCREW	STEEL	GALVANIZED

INITIAL RELEASE	N.S.	02/26/2016	
SYM.	REVISION DESCRIPTION	APP	DATE

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
4" OCTAGON BOX 1-1/2" DEEP BOX WITH 1/2" KNOCKOUTS & RAISED GROUND

TOLERANCE UNLESS OTHERWISE SPECIFIED
.XX DECIMAL ±.015
.XXX DECIMAL ±.005
ANGLE ±2°

RACO
South Bend, Indiana

DRAWN BY:	J.R.	SCALE:
APP. BY:	N.S.	1:2
DATE:	02/26/2016	

8125 CUS

8125 DIMENSION SHEET FOR CAT. NO.

SIZE: **A**