



REVISIONS			
REV.	DATE	DESCRIPTION	BY
-	06-23-21	INITIAL RELEASE	RMV



DRAWN BOX
#8-32 x 1/2 TRI LOBE SCREW

PIGTAIL:
WIRE: #12 AWG STRANDED, 10-1/2" LONG, GREEN INSULATED, U.L. LISTED, 600 VOLT MAX; EXTRA-GRIP RING TERMINAL, 16/12 AWG BRASS; #10-32 X 3/8" GROUND SCREW W/COMBO HEX WASHER HEAD (SLOTTED, #2 PHILLIPS AND ROBERTSON)

DESCRIPTION	MATERIAL	FINISH
PIG TAIL	COPPER	SEE NOTES
FASTENERS	STEEL	GALVANIZED
DRAWN BOX	STEEL	GALVANIZED

LIST OF PARTS

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
4" SQ. X 1-1/2" DP. OUTLET BOX, 1/2"-3/4" KOs, W/ GROUND PIGTAIL

- NOTES:
1. ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 2. BOX VOLUME: 21.0 IN³ [344.1 CM³]
 3. cULus LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
1/2" KO	A, B, C, D, E	2
3/4" KO	A, B, C, D	1
3/4" KO	E	1

TOLERANCE UNLESS OTHERWISE SPECIFIED

.XX DECIMAL ± .015
.XXX DECIMAL ± .005
ANGLE ± 2°

RACO

DRAWN BY: RMV
APP. BY: N.S.
DATE: 06-23-21

SCALE: 1:2

SIZE: **A**