



LIST OF PARTS		
DESCRIPTION	MATERIAL	FINISH
SPACER	STEEL	GALVANIZED
SIDE	STEEL	GALVANIZED
BOX SCREW	STEEL	GALVANIZED
X CLAMP	STEEL	GALVANIZED
CLAMP SCREW	STEEL	GALVANIZED

X CLAMP ACCEPTS ALL OF THE FOLLOWING WIRE TYPES:

- STEEL & ALUMINUM BX: .444" [11.27 MM] O.D. TO LARGEST THAT WILL FIT IN CLAMP
- STEEL MCI: .425" [10.79 MM] TO .600" [15.24 MM] O.D.
- ALUMINUM MCI: .400" [10.16 MM] TO .495" [12.57 MM] O.D.
- FLEXIBLE METAL CONDUIT: 3/8" TRADE SIZE

- NOTES:
- ALL DIMENSIONS ARE IN INCHES AND [MILLIMETERS]
 - BOX VOLUME: 21.0 IN³ [344.1] CM³
 - UL LISTED

KNOCKOUTS		
TRADE SIZE	LOCATION	QTY.
(1/2"-3/4") TKO®	B,C	1
1/2" KO	B,C	2
1/2" KO	A	1

SYM.	REVISION DESCRIPTION	APP	DATE
	INITIAL RELEASE	N.S.	02/29/2016

THE DESIGN AND DIMENSIONS OF THE PRODUCT SHOWN ON THIS DRAWING ARE SUBJECT TO CHANGE WITHOUT NOTICE

TITLE:
4" SQUARE BOX 1-1/2" WITH X CLAMPS

<p>RACO South Bend, Indiana</p>		SCALE:	B
		DATE:	
<p>TOLERANCE UNLESS OTHERWISE SPECIFIED</p> <p>.XX DECIMAL ±.015 .XXX DECIMAL ±.005 ANGLE ±2°</p>		<p>DRAWN BY: J.R.</p> <p>APP. BY: N.S.</p> <p>DATE: 02/29/2016</p>	